


Handle display Handle color optional



12*20mm



12*35mm



12*20mm



12*35mm

产品特点：

1. 采用 Dual-TEC 双冷却系统，


2. 采用 24 小时不间断工作，可连续工作 24 小时，无需休息。



Just One minute!
Quick cooling down to **-25°C**



Three Waves 755nm 808nm 1064nm, 755nm (Alexandrite) 808nm (Diode) 1064nm (Nd:YAG).
755nm (Alexandrite) 808nm (Diode) 1064nm (Nd:YAG).
808nm (Diode) 1064nm (Nd:YAG).
1064nm (Nd:YAG) 808nm (Diode) 755nm (Alexandrite).






ALEX 755nm
For white skin
 (fine, golden hair removal)




SPEED 810nm
For yellow neutral skin
 (brown hair removal)



YAG 1064nm
For black skin
 (black hair removal)



Treatment Comparison





Smayer 755nm

Smayer 755nm/1064nm 3000W;
 Smayer 0-150J/cm2 (0.1-150J/cm2)
 Smayer 10-800ms (10-800ms);
 Smayer 1-10 cm;
 Smayer 20*12/35*12 cm
 Smayer LCD 12"---10.4" TFT True Color LCD
 Smayer TEC
 Smayer 16 12 10 cm
 Smayer 115*59*61 cm

OEM ,ODM

- .Smayer 755nm/1064nm 3000W, Smayer 0.1-150J/cm2 (0.1-150J/cm2)
- .Smayer 10-800ms (10-800ms);
- .Smayer 1-10 cm;
- .Smayer 20*12/35*12 cm
- .Smayer LCD 12"---10.4" TFT True Color LCD
- .Smayer TEC
- .Smayer 16 12 10 cm
- .Smayer 115*59*61 cm

Certificate display

Certificate is the best guarantee for you



Packing

safe and thoughtful packaging service



Built-in prevention Collision bubble

Two-year warranty for machine handle as consumable,
one-year warranty.

OEM&ODM service for distributor.

Tight packaging

Training: (Video+Manual+Online Service)
Can Keep You Operate It Easily.



3-5 business days delivery

Professional guide:
24 Hours Professional online customer service,