



From Israel Technology

FOR ALL SKIN TYPE HAIR REMOVAL

- 100% Ice Cooling
- 100% Permanent
- 100% Painless

.
 ;
 ;
 .
 ;
 808 *nm 7558081064 nm;

350g
 Ultra light handle



12x36mm

Handle

1800W diode laser hair removal



12x24 mm


Handle

1200W diode laser hair removal

Three Waves 755 nm 808nm 1064nm, .

755nm .()

808nm .() () () () () ()
1064nm () () () () () () ().




ALEX 755nm
For white skin
(fine, golden hair removal)



SPEED 810nm
For yellow neutral skin
(brown hair removal)



YAG 1064nm
For black skin
(black hair removal)



Treatment Comparison

