

SAFE AND PAINLESS

DIODE LASER HAIR REMOVAL MACHINE

LEARN MORE



ICE MLKJ! ,

15 Years Laser Beauty Device Manuafactor

• High Feedback
Top10 Supplier

• OEM & ODM
SERVICE



• *Cooling effect* •

The handle is frosted for one minute,
making your treatment more comfortable and painless



Suitable for hair removal on any part of the body,
Such as arms, legs, face, armpits, back, chest, etc.



*1800 0000 0000w 0000 000 0000 00000 ,0000 00000 000000000 00 00000 000000!

* 00000 0000000 .000 0000000 0000 000000 0000 0000 0000 0000 00000 0000 000000 000000 0000000 0000 000000 00 0000000 0000000 0000 ,00000 00 00000000000 0000000 00000000 0000000 00000 00000 00000 6 0000 00000000 00 00.

* 00 ...000000 ,000000 ,00 ,000 ,000 000 ,000000 ,0000 000 0000000 0000 00 0000 000 000000
0000 000000 00 00.

* 1-10 000HZ.treatment fastly!!! 000000 0000 .000000 000000 00000 000000 000000!!



1064 nm

[illegible]

For all skin types

Triple wavelength laser work together

755
nm

808
nm

1064
nm

755nm/808nm/1064nm

755nm
808nm
1064nm

Laser hair removal treatment theory



Hair active growth phase(3-6years)



laser treatment



Transition phase (1-2weeks)



Resting phase (1-2 weeks)



Return to growth phase

808V29

808V29

808 755/808/1064

808 755/808/1064 755nm 3 755nm 808nm 1064nm

4 '14 14K

4 '14 14K 14K 14K

755/808/1064

755/808/1064

20-40

20-40 20-40 20-40

10~150 j/cm2,

10~150 j/cm2, 10~150 j/cm2

1-10HZ

1-10HZ

3500W

3500W

12*24

12*24 12*24 12*24 36*12 36*12 36*12

110V/60HZ

110V/60HZ 220 220V/50HZ 220V/50HZ

95

95 95 95

105

105 105 105

53*40*105

53*40*105 53*40*105 53*40*105

125*56*70.4

125*56*70.4



Painless 810nm-755nm
Diode laser handle
Suitable for all skin tones and body parts

125*56*70.4

125*56*70.4

125*56*70.4

* 125*56*70.4

* 125*56*70.4

* 125*56*70.4

* 125*56*70.4

Custom Section

LOGO design



SYSTEM design



10000 10000 1000

100 100000 100 100 100000 10000 100 10 100000 100000 10000 1000



Our customers

60000+ CUSTOMERS



102

Countries

OEM/ODM

Customize the machine according to customer needs

CERTIFICATE



我们 拥有 14 个 国家 的 专利 证书!

13 个 国家 的 专利 证书

我们 拥有 CE 认证 和 TUVcertificates 认证

我们 拥有 & OEM

我们 拥有

我们 拥有 专利 证书 , 我们 拥有 专利 证书 , 我们 拥有 专利 证书 , 我们 拥有 专利 证书 , 我们 拥有 专利 证书 , 我们 拥有 专利 证书 !

Packing

safe and thoughtful packaging service



Built-in prevention Collision bubble

Two-year warranty for machine handle as consumable,
one-year warranty.

OEM&ODM service for distributor.

Tight packaging

Training: (Video+Manual+Online Service)
Can Keep You Operate It Easily.



3-5 business days delivery

Professional guide:

24 Hours Professional online customer service,