



DIODE LASER HAIR REMOVAL MACHINE

- SUPER ICE PAINLESS EXPERIENCE
- PERMANENT HAIR REMOVAL
- COMFORTABLE HAIR REMOVAL

1min} Fast and painless hair removal
One minute cooling -21°C



Large Spot Size

Quick and Comfortable

With large spot size of 1.2*3.5cm², for faster treatments and better patient experience.



TEC Plus

Continuous Contact Cooling

TEC is an advanced technology that continuously cools skin and facilitates range-controlled temperature throughout the entire treatment. Patients can now enjoy a completely pain-free, cool and comfortable experience throughout the session.

□□□□

* □□□□□□ 40 □□ □□□□□□□□ ,□□□□□□ □□□□ □□□□ □□□□
1000 □□ 10 □□□□□□□□□□*W, 12 1200 □□W 1600 □□ 16-□W
*□□□□□□□□ □"□ 38*12 ,□"□ 25*15 ,□"□ 20*12 □□□□□□ □□□□□□
□□□□□□ □□□□□□ □□□□□□ □□□□□□ □□ ,□□□□ □□ □□□□ 450 □□□□□□*
□□□□□ □□□□□□□□ , (□□□□□□ □□□□□□ □□) □□□□□□□ □□□□ □□ □□ □□□□□□ □□□□ □□ □□□□□□ □□ □□

Handle Details


Three Wavelengths Work Togher





12*20nm


755nm Laser
808nm Laser
1064nm Laser





12*35nm

755nm Laser
808nm Laser
1064nm Laser




□□□□ □□□□ □□□ □□□□ □□□□□□

Alex 755nm □□□□ □□□□
808 □□□□□□ □□□□□□nm □□□□ □□□□
Long Pulse 1064nm □□□□ □□□ □□□□

Working Principle

Triple wavelength laser work together

Suits for all skin and hair types



- **755nm for white skin** (fine, golden hair removal)
- **808nm for yellow neutral skin** (brown hair removal)
- **1064nm for black skin** (black hair removal)

□□□□ □□□



□□□□ □□□□

1. □□□□ □□□ , '□□□□ 12.4 □□□□ □□□□
- □□□□□ □□□□□ □□□ □□□□ 6 ,□□□□ □□□□ 6 ,□□□□□ □□□□ .2
- □□□□ □□□ □□ □□□□□□ □□□□□ ,□□□□ □□□□□□□□□□ 6 .3
- □□□□□ .4 OEM □□□□□/□□□□□) □□□□□□□□□□...