



IPPL 150,000-30,000

IPPL 50*15 . 150,000-30,000 , . LCD 8.4 TFT,

conten t



IPPL 150,000-30,000

Elight Handle Design



Specification

Optional Spot Size:
15*50mm

Imported UK lamp

Long shots time:
150,000--300,000 times

7filters:
420/510/560/585/640/690/755nm

Super cooling system



Elight 8.4 光面型 光面型 光面型 , 光面型 光面型 光面型 .



Elight 8.4 光面型 光面型 光面型 光面型 光面型

1. Elight 8.4 光面型 光面型 光面型

2. 6 years warranty , OEM/ODM
3. 8.4 inch touch screen
4. OEM (OEM/ODM) (OEM/ODM)...

Screen interfac

Professional Screen, Easy operation



Main Menu

8.4 inch true color big touch screen
Super cool touch Experience.



IPL mode:

5 options for skin treatment



IPL mode:

operation interface




Multi-language screen:

6 languages for your choice



System setting



System setting

8.4 inch touch screen

1200W TEC 1-3

150,000-30,000

8.4 inch touch screen

1200W TEC 1-3

150,000-30,000

8.4 inch touch screen

1200W TEC 1-3

150,000-30,000

8.4 inch touch screen

1200W TEC 1-3

IPL: 50*15 inch touch screen

420/510/560/585/640/690/755

150,000-30,000

8.4 inch touch screen

1200W TEC 1-3

150,000-30,000

8.4 inch touch screen, AU, 110V 220V

30 inch

8.4 inch touch screen

1200W TEC 1-3

Multi-angle display



Left view



Front view



right elevation