

A composite image featuring a woman's legs on the left and a diode laser hair removal machine on the right. The woman's legs are bare and positioned as if she is standing. The machine is black with a control panel on top that includes a small screen and several buttons. A stylized, wavy white line graphic connects the two elements.

DIODE LASER HAIR REMOVAL

PAINLESS HAIR REMOVAL, NO SIDE EFFECT

MORE

Sync to machine

SMART CLING

Intelligent | Interconnected | Efficient



□□□□□□□□ □□□□ □□□□□□

1. □ □□□□□-Bluetooth/□□□□□□ wifi/□□□□□□ □□□□□□/□□□□□ □□□□□□/□□□□□□□ □□□□ □□□□□ □□ □□□□□
- 2.
- 3.
- 4.
- 5.

Frequency	Pulse	Energy	Total	Date
5	30	78	0	2023-05-08 11:25:11
5	30	78	0	2023-05-08 11:25:13
5	30	78	0	2023-05-08 11:25:17
5	30	78	0	2023-05-08 11:25:19

Multimedia Control System

Supports Bluetooth /Wifi /Remote control and locking/Cloud storage



* □□□□ □□□□□□ □□□□□□□□□□ □□□□□□ □□ □□□□□□ □□□□□□.

15.6" Smart Clinic Multimedia Monitor with HD 4K Screen



* 15.6" Smart Clinic Multimedia Monitor with HD 4K Screen.

* 15.6" Smart Clinic Multimedia Monitor with HD 4K Screen.

15.6" Smart Clinic Multimedia Monitor with HD 4K Screen

. 15.6" Smart Clinic Multimedia Monitor with HD 4K Screen (755 (nm808nm1064nm) 15.6" Smart Clinic Multimedia Monitor with HD 4K Screen, 15.6" Smart Clinic Multimedia Monitor with HD 4K Screen.

15.6" Smart Clinic Multimedia Monitor with HD 4K Screen 36*12 / 24*12 15.6" Smart Clinic Multimedia Monitor with HD 4K Screen ! 15.6" Smart Clinic Multimedia Monitor with HD 4K Screen.

4. (15.6" Smart Clinic Multimedia Monitor with HD 4K Screen, 15.6" Smart Clinic Multimedia Monitor with HD 4K Screen, 15.6" Smart Clinic Multimedia Monitor with HD 4K Screen (4K 15.6" Smart Clinic Multimedia Monitor with HD 4K Screen).

16, '16

6, 6, .(

16 .(

(OEM ODM / /) ...)

350g

Ultra light handle



12×36mm

Handle

1800W diode laser hair removal



12×24 mm

Handle

1200W diode laser hair removal

16, '16

6, 6, .(

16 .(

(OEM ODM / /) ...)

LASER COMPARISON

【Other - Lasers】



- ✓ The original structure is not light enough.
- ✓ Big dimension.
- ✓ Short life.

【2022-MLKJ-Lasers】



- ♥ Lighter weight.
- ♥ Smaller dimension.
- ♥ More advanced structure design.
- ♥ More advanced performance.

【2022-MLKJ-Medical-Lasers】



- ♣ More advanced packaging technology.
- ♣ Higher energy densit.
- ♣ Lighter appearance.
- ♣ Longer life.

What can
we do
in
1 MINUTE

Time for a cup of instant coffee,
the handle can quickly frost.




EXFU[®]
Simple · Safe · Enjoy



sdqym.en.alibaba.com

Suitable for hair removal on any part of the body,
Such as arms, legs, face, armpits, back, chest, etc.



□□□□□ □□□□□ □□□□□□ ,□□□□□ □□□□□ □□□□□□ □□.



IT'S TOO TO FAST

Easy to realize rental control,
Treatment data synchronization.



Android OS



Touch Screen



Built-in Speaker

□□□□□□ □□□□□□ ,□□□□□□ □□□□□□!