



*D10*

**Portable Hair Removal Machine**

Three bands: 755nm/808nm/1064nm  
Suitable for all skin types

**DIODE LASER** hair removal machine

■ 2 Years Warranty ■ OEM / ODM Service ■ 3 waves 1064nm + 808nm + 755nm



DIODE LASER 1064nm 808nm 755nm **D10**

- \* 12—8 英寸 1200W 激光 脱毛 机 1064nm 808nm 755nm 三 波 长 。
- \* 1064nm 808nm 755nm 三 波 长 激光 脱毛 机 3-5 分钟 , 脱毛 率 达 90% 。
- \* 3 1064 1064nm 808nm 755nm, 3 波 长 激光 脱毛 机 1-2 。

# Handle Display

Two colors, two spot sizes are optional



755 :□□□□ □□□□ □□ □□□□nm 808nm 1064nm

755nm □□□□ □□□□ □□□□ □□□□□□□□.

808nm □□□□ □□□□□□□□ □□□□ □□□□□□□□.

1064nm □□□□ □□□□ □□□□ □□□□□□□□.

# *Working Principle*

755nm and 808nm and 1064nm , suits for all skin and hair types.



**ALEX 755nm**

**For white skin**

(fine, golden hair removal )



**SPEED 810nm**

**For yellow neutral skin**

(brown hair removal)



**YAG 1064nm**

**For black skin**

(black hair removal)

# The real experience is visible

Through live test verification ,safe ,long,painless  
and effective



- 1) .14 14 : (2
- 2) : (3 OEM: ,



# Product details

Ultra-thin large screen, cool light strip



!000000 0000000 0000 ,0000000 00000000  
000000000 0000 24!