

□□□□ OEM / ODM
 □□□□ □□ □□ ,□□□□ □□

Build more trusted partners

Our customers

60000+ CUSTOMERS

OEM/ODM

Customize the machine according to customer needs



CERTIFICATE

Obtained multi-way authoritative certification,
 product testing certification, product patent authority,



□□□□□□

*.□□□□ □□□□□□ □□ □"□□□ □□□□□ □□□□ □□

.□□□□ □□□□ □□□□□□ □□□□ □□ □□□□ 3-□ □□□□ ,□□□□□ □□□□□□ 40-□ □□□□ *

808 *nm □□□□ □□□□ □□□ □□□□□□ □□□□

1200 □□ □□□□ □□□□ :□□□□ □□□□ *W /1800W □□□□□□□□□□

!□□□□ □□□□ □□□□ □□□□□□ □□□□ ,□"□ 36*12 □□ □"□ 24*12 □□□□□ □□□□□ □□□□□ □□□□ *

□□□□□ □□□□□ :□□□□□ □□□□□ * Dual-TEC 24 ,□□□□ □□ □□□□□□ □□ □□□□□ □□□□□ □□□□□ □□□□□□□□□□ ,□□□□□□□□

.□□□□□ □□□ □□□ □□□□

□□□□□ □□□□□□ 40 :□□□□□□□ □□□□□ *

□□□□ □□□□□□

12*24mm or 12*36mm handle

Suitable for any unwanted hair on areas like face, arms, armpits, chest, back, bikini, legs...



1200w, 1800w 1000000 1000000 1000 1000
1000 36*12 1000 24*12 1000 1000
*350 100000 100000 100000 100000 ,10000 1000 ,1000000 10000 1000

* 10000 100000 , (1000000 1000000 1000) 1000000 1000 1000000 1000 ,100000 100000 1000



1000000000000


* 1000 10000 10000 ,100000 100000 ,1000000 1000 10000

* 100% 100% 100% 100% 100% 100% 100% 100%
 * 100% 100% 100% 100% 100% 100% 100% 100%
 100% 100%

Hair removal comparison

The real picture taken by the customer

Different parts of men and women, as well as different skin colors can have very good hair removal results, they all get a permanent and painless hair removal experience



Before



After Treatment

Hair removal comparison

The real picture taken by the customer

Different parts of men and women, as well as different skin colors can have very good hair removal results, they all get a permanent and painless hair removal experience



Before



After Treatment

100% 100%

100% 100% ,14 100% 100% 100%
 100% 100% 100% 100% 6 ,100% 100% 6 ,100% 100% .2
 100% 100% 100% 100% ,100% 100% 6 .3
 100% 100% .4 OEM 100%/100% 100%...)

5. 100% OEM/ODM

- >>OEM your own machine body
- >>OEM your own program software
- >>OEM pretty machine colors
- >>Print your LOGO on machine body and screen
- >>R & D team and Quality inspection Show

6.

	808V19
	18 , 12 , "
	4 ' 14 K
	808 " 1064 " 808 " 755 "
	20-40
	10~150 j/cm2,
	1-10HZ
	TEC
	3500W
	12*24 " 36*12 "
	110V/60HZ 220 V/50HZ
	95 "
	105 "
	53*40*105 "
	125*56*70.4

	3-7
	, DHL, TNT, Fedex
	, :
	,

Packing

safe and thoughtful packaging service



Built-in prevention Collision bubble

Two-year warranty for machine handle as consumable,
one-year warranty.

OEM&ODM service for distributor.

Tight packaging

Training: (Video+Manual+Online Service)
Can Keep You Operate It Easily.



3-5 business days delivery

Professional guide:
24 Hours Professional online customer service,