



From Israel Technology

FOR ALL SKIN TYPE HAIR REMOVAL

- 100% Ice Cooling
- 100% Permanent
- 100% Painless

.

;

;

.

;

808

*nm 7558081064

350g
Ultra light handle



12x24 mm
Handle
1200W diode laser hair removal




12x36mm
Handle
1800W diode laser hair removal

Three Waves 755nm 808nm 1064nm, 755nm Alex, 808nm Speed, 1064nm YAG.

755nm (Alex) 755nm 755nm 755nm 755nm

808nm (Speed) 808nm 808nm 808nm 808nm

1064nm (YAG) 1064nm 1064nm 1064nm 1064nm




ALEX 755nm
For white skin
 (fine, golden hair removal)



SPEED 810nm
For yellow neutral skin
 (brown hair removal)



YAG 1064nm
For black skin
 (black hair removal)



Treatment Comparison

