

# 2021 Salon Queen

FASTER: 60% FASTER  
 STRONGER: STRONGER POWER 40%  
 BETTER RESULT  
 SMARTER: 4K ANDROID SCREEN



FASTER, STRONGER, SMARTER

1. 4K ANDROID SCREEN
2. 40,000,000 PULSES PER TREATMENT HEAD
3. 60% FASTER
4. 40% STRONGER POWER
5. 5.14.0 ANDROID SYSTEM
6. 4K ANDROID SCREEN



V26

Super comfortable experience  
 Painless and permanent treatment result  
 Suitable for all skin types and body areas

TEC 4K ANDROID SCREEN 40,000,000 PULSES PER TREATMENT HEAD 60% FASTER 40% STRONGER POWER 5.14.0 ANDROID SYSTEM 4K ANDROID SCREEN

24 小時服務熱線 歡迎各界人士垂詢。地址：廣東省深圳市光明區新湖街道新湖社區新湖大道東 10 號。電話：0755-2719 1111。傳真：0755-2719 1112。郵箱：sz@szlaser.com.cn。公司網址：www.szlaser.com.cn。
   
1) 10 英寸。適用於 10-40 厘米，16 英寸 / 12 英寸。
   
2) 適用於 35\*12 厘米 / 20\*12 厘米。適用於 2 英寸。
   
3) 適用於 35 厘米，適用於 20 厘米。
   
4) 適用於 35 厘米。
   
5) 適用於 350 厘米。
   
. 適用於 14.1 英寸。
   
. 適用於 6 英寸。
   
. 適用於 6.3 英寸。
   
. 4 OEM (適用於...)

適用範圍	16 英寸, 12 英寸, 10 英寸, 8 英寸, 適用於 16 英寸/12 英寸
適用材料	755nm 808nm 1064nm/ 808 納米 適用於
適用功率	0-150J/cm2
適用速度	1-10 英寸
適用時間	40-800ms
顯示屏	LCD 14.0 TFT True Color
適用功率	4000W
適用電壓	220V/50HZ 110 伏/60HZ
N.W/ G.W	62 英寸 78/英寸

## Company Strength

**50+**  
R&D team

**500+**  
Cooperation Case

**17 Days**  
Product deadline

**100+**  
Export country

- >>OEM your own machine body.
- >>OEM your own program software.
- >>OEM pretty machine colors.
- >>Print your LOGO on machine body and screen.

# Custom Section


## CASE design



## LOGO design



## SYSTEM design



□□□□ □□□□


# CERTIFICATE DISPLAY





# Packing

safe and thoughtful packaging service



## Built-in prevention Collision bubble

Two-year warranty for machine handle as consumable,  
one-year warranty.

**OEM&ODM service for distributor.**

## Tight packaging

Training: (Video+Manual+Online Service)  
Can Keep You Operate It Easily.



## 3-5 business days delivery

Professional guide:  
24 Hours Professional online customer service,

