



□□□□□ □□ □□□□□ □□□ .□□□□□□ □□□□□ □□□□□ □□ □□□□□ □□□ □□□□□ □□□□□ 24 □□□□□ □□□□□ !!

Diode Laser

For You. For Life.



0000000 0000 0000 000000 000000 1064 808 755 00 000000

- 1) 0000 000000 TEC, 000000 ,0000 24 0000 0000 000000 000000 000000 0000 ,0000 000 000000 0000 00 00 .0000
- 40,000,000-0 0000 0000 0000 0000 ,00000000 00000000 0000 000 00000000 000000 (2
- .00000 00000000 0000 1 ,000 00000000 0000 1 ,00000000 2 (3
- 1600 0000 0000 000 (4w, 000 00000 00000 00000 000 ,00000 00000000.

350g lightweight **handle**, more ergonomic

Available in **black or white**



755 808 1064 1000000 1000000 10000 100000 10000 10000

1000 1000 10 ,0" 20*12 1000 1000w.

1200 1000 12 ,0" 35*12 1000 1000w.

1600 1000 16 ,0" 35*12 1000 1000w.

1000 1000 1000000 10000 ,1000000 10000

1000 1000 1000000 1000000 1000000 10 100000 1000 1000 100000 1000 10000






755 808 1064 000000 000000 0000 000000 0000 0000

- 1) 000000 0000 000000 00000000 0000 0000
- 2) 0000 0000 000 000000 0000000000 0000 0000
000000 000 00000 000000 ,0000 00000000 0000 00000000 (3.



00000 0000 000 000 ,0000000 000000 00000








1. 14.1 英寸触摸屏
 2. 6 英寸触摸屏, 触摸屏/触摸屏
 3. 触摸屏
 4. OEM (触摸屏/触摸屏) 触摸屏...

The new **14-inch 4K** screen

Support system customization



产品特点 产品特点

产品	755 产品 产品 nm808nm1064nm
产品 产品	产品 16 --- 产品 8 ,产品 产品
产品 产品 产品	100 产品
产品 产品	产品 14 产品 产品 产品 产品 产品'
产品 产品	808nm 808 产品 nm755nm1064nm
产品 产品	12*35 产品 20*12/产品
产品 产品 产品 产品 产品	808 产品 10,000,000-40,000,000 产品 :产品
产品 产品	10-150 J/cm2 150 产品 产品 J/cm2 产品 产品)
产品 产品	40 ~ 800ms 产品
产品	1.0-10 产品;
产品 产品	产品 产品 产品 TEC 产品 产品 产品
产品 产品	800w/1000w/1200w/1600w
产品 产品	2000W
产品 产品	220V/50HZ 110 产品 V/60HZ
产品 产品 产品	-10~3 产品 产品
产品 产品 产品	27~31 产品 产品
产品 产品	AC220V/110V 50~60Hz

产品 产品 ,产品 产品 产品!