

. 808nm 755nm 1064nm
 ; 808nm 755nm 1064nm .
 ; 808nm 755nm 1064nm *
 . 808nm 755nm 1064nm *
 ; 808nm 755nm 1064nm 808nm 755nm 1064nm *
 808nm 755nm 1064nm 808nm 755nm 1064nm *nm 7558081064

350g
 Ultra light handle




12×36mm
Handle
 1800W diode laser hair removal



12×24 mm
Handle
 1200W diode laser hair removal

Three Waves 755nm 808nm 1064nm, 808nm 755nm 1064nm, 808nm 755nm 1064nm.

755nm .(808nm/755nm) 808nm 755nm 1064nm
 808nm .(808nm) 808nm 755nm 1064nm
 1064nm .(1064nm) 808nm 755nm 1064nm
 808nm 755nm 1064nm 808nm 755nm 1064nm 808nm 755nm 1064nm






ALEX 755nm
For white skin
(fine, golden hair removal)



SPEED 810nm
For yellow neutral skin
(brown hair removal)



YAG 1064nm
For black skin
(black hair removal)



Treatment Comparison

