

**2in1 multifunctional combined
hair removal machine**

*Hair removal and skin rejuvenation
One machine double effect*



808+Elight

□□□□□□ □□□□□□

Real shot display



808 handle



Elight handle




Elight/IPL 150,000-30,000 , 755 : *nm808nm1064nm


* 150,000-30,000 , 755 : *nm808nm1064nm

Three wavelengths work together

12*24mm² {




12*35mm² {



**Suitable for hair removal on any part of the body,
Such as arms, legs, face, armpits, back, chest, etc.**





ELIGHT HANDLE

specification

- High-quality: Elight handpiece with super cooling system
- Optional Spot Size 15*50mm, 15*35mm
- Long shots time: 150000 times
- 7 filters: 420/510/560/585/640/690/755nm
Standard: 420/510/680nm



Before and after



Skin rejuvenation



Freckle removal



wrinkle reduction



Acne clearance



Hair removal



Pigmentation treatment

Hair removal and skin rejuvenation one machine and two effects

2in1 Multifunction



808 handle

Painless hair removal, Permanent hair removal,
Suitable for all skin tones.



Elight handle

Elight for hair removal, skin rejuvenation,
vascular therapy, pigmentation therapy, acne therapy.

7-ADVANTAGE

• Counter

The handle is equipped with an energy counter to clearly understand the total count during use.



• German imported laser

808 handle adopts Germany imported laser, which has stronger energy and long service life.

• Big spot size

808 handle uses large light spot of 12× 35 mm, with large processing area and higher working efficiency. The E light handle uses a 15 × 50 mm large light spot.



808 handle

E light handle

• Cooling Effect

The handle adopts refrigeration effect, which can effectively cool the skin in the treatment process and improve the comfort of treatment.

• E light lamp

The e light handle uses IPL lamps imported from the United Kingdom, which emit light up to 150,000 times and have a longer service life.




• Rf function

The e light handle is added with RF function, and the RF function after depilation can achieve the effect of tightening and lifting.

• Optical filter


The e light handle is equipped with seven filters, which can be used for different treatments and different skin colors to select the corresponding filters, thus making the operation more convenient.



14inch true touch screen

6 kinds skin type for choice. accept ODM OEM Service.

The new **14-inch** screen is clear easy to operate.



24寸触摸屏，操作简单，接受ODM/OEM服务。