

**High power diode laser
with nice cooling technology
for hair removal with painless!**


* 1-10 HZ. 00000 0000 .000000 00000 00000 00000 !!!0000 00000!!



755 nm



808 nm




1064 nm



755 nm for white skin (fine, golden hair removal);



808 nm for yellow neutral skin (brown hair removal);



1064 nm for black skin (black hair removal)

□□□□ □□□□

1. □□□□ □□□□ □□□□□□ □□□□□.
 2. □□□□ □□□□□□ □□□□ □□□□□ 40,000,000 ,□□□□□□□□ □"□□□□ □□ □□□□□□□□ □□□□□□□□ □□□□□□ □□□□□.
 3. □□□□ ,□□□□□□ □□□□ ,□□□□□□ ,□□□□□□
 4. □□□□□□ □□□□ □□□□ □□□□□ □□□□□□
- □□□□□ 6 □□ '□□□□□ 5.14.0 □□□□□□ □□□□□□ □□□□□□□□ □□□□ □□□□.

Handle Details

Three Wavelengths Work Together



755nm 808nm 1064nm, 3 Wavelengths Work Together, 755nm 808nm 1064nm, 755nm 808nm 1064nm, 755nm 808nm 1064nm, 755nm 808nm 1064nm.

755nm (755nm/808nm) 808nm 1064nm 1064nm

808nm (808nm) 755nm 1064nm 1064nm

1064nm (1064nm) 755nm 808nm 808nm.

For all skin types

Triple wavelength laser work together

755
nm

808
nm

1064
nm

755nm/808nm/1064nm

755nm
808nm
1064nm

Laser hair removal treatment theory



Hair active growth
phase(3-6years)



laser treatment



Transition phase
(1-2weeks)



Resting phase
(1-2 weeks)



Return to growth
phase

□□□□ □□□□□□







产品名称	808V29
产品型号	808 半导体 激光nm 755/808/1064 nm 3 通道 激光
产品规格	4 '通道 14 通道K 通道 通道
产品重量	755/808/1064
产品功率	20-40 通道 通道
产品频率	10~150 j/cm2, 通道
产品波长	1-10HZ
产品功率	通道
产品功率	3500W
产品尺寸	12*24 通道 36*12 通道
产品电压	110V/60HZ 220 V/50HZ 通道
产品重量	95 通道
产品重量	105 通道
产品重量	53*40*105 通道

125*56*70.4

Before and After



After



After

□ □ □ □ □ □ □ □

* □□□□ □□□□□□ □□□□□□

* □□□□ □□□□□□ □□□□ □□□□□□□□ □□□ □□□□□□ □□

[illegible]

Custom Section

LOGO design



SYSTEM design



0000 000000 0000 0000 000000 000000 0000 00 000000 0000000 00000 0000

Our customers

60000+ CUSTOMERS



102

Countries

OEM/ODM

Customize the machine according to customer needs

CERTIFICATE



PACKING

Safe and thoughtful packaging service



Built-in prevention
collision bubble

Two- year warranty for machine
handle as consumable,
one-year warranty

Tight packaging

Training:
(video +manual+online service)
can keep you operate it easily



3-5 business days
delivery

professional guide:
24 hours professional online
customer service