

A woman's legs are shown from the knees down, with her hands resting on her thighs. To the right is a black diode laser machine with a control panel featuring a small screen and several buttons. A white, wavy, smoke-like effect emanates from the machine's handle.

DIODE LASER HAIR REMOVAL

PAINLESS HAIR REMOVAL, NO SIDE EFFECT

MORE

A close-up of a woman's arm and shoulder, showing smooth skin. To the left is a black diode laser machine with a control panel that has a small screen displaying a group of people. A blue diagonal line runs across the bottom of the image.

Diode Laser

Permanent hair removal

□□□□□□ □□□□□ □□□□□□□□□□ □□□□ □□□□ □□ □□

1. 0.01mm 0.01mm 0.01mm 0.01mm 0.01mm 15- μ 0.01mm 0.01mm 0.01mm.
2. 0.01mm 0.01mm ,0.01mm 0.01mm 0.01mm 0.01mm 0.01mm 0.01mm .0.01mm.
3. 0.01mm 0.01mm 0.01mm 0.01mm 0.01mm ,0.01mm 0.01mm.
4. 755 :0.01mm 0.01mm .0.01mmnm 808nm1064nm, 0.01mm 0.01mm 0.01mm ,0.01mm 0.01mm 0.01mm 0.01mm 0.01mm 0.01mm .
5. 0.01mm 0.01mm ,0.01mm 0.01mm 0.01mm 0.01mm ,0.01mm 0.01mm 50 ,0.01mm 0.01mm 0.01mm .0.01mm 0.01mm 0.01mm.

12*24mm or 12*36mm handle



- >>> Big 20*12 □□□□□ □□□□mm, 12*35mm for option
>>> Laser technology, big power 10bar 1200W, 12 bar 1800W
>>> 300g handle, light weight, free quick slide treatment



>>> New nose hair treatment head, applicable to small part treatment
>>> 1 minute refrigeration frosting, painless treatment experience






ALEX 755nm
For white skin
 (fine, golden hair removal)



SPEED 810nm
For yellow neutral skin
 (brown hair removal)



YAG 1064nm
For black skin
 (black hair removal)



Treatment Effect

This is the clinical result of hair removal
It takes 3--5 times to realize
permanently hair removal



- * 4 * 14 K 14 * 14 K 14 *
- * OEM * OEM *
- * * *

מפרט של מכונה להסרת שיער בלייזר דיודה

פריט	755nm808nm1064nmלייזר דיודה אנכי
סוג לייזר	בר לייזר רפואי דיודה לייזר: 10 בריס/15 בריס
כוחו של כל בר	120w/Barרפואי עם
מערכת תצוגה	'מסך מגע בצבע אמיתי בגודל 14 אינץ'
אורך גל	808nm/755nm/1064nm
Spot Size	24*12mm ² /12*36mm ² רפואי עם
תוחלת חיים של ידית לייזר	לפחות 40 מיליון יריות
אנרגיה	(אופציונלי J/cm ²)/מתכוון (עד 10-150 J/cm ² 150)
משך הדופק	30 ~ 400ms מתכוון
תדירות	1.0-10 הרץ;
מערכת קירור	קומפרטוראוורסגור זרימת מים
ידית כוח	1000w/1200w/1600w/1800w
כוח מכונה	4000 וואט
מקור חשמל	220V/50HZ 110V/60HZ או
טמפרטורת קריסטל	-20~3 מעלות צלזיוס
טמפרטורת המכונה	24 מעלות צלזיוס
דרישת חשמל	AC220V/110V 50~60Hz



אנרגיה OEM, ODM :אנרגיה

- אנרגיה של 1000W.
- אנרגיה של 1200W.
- אנרגיה של 1600W.
- אנרגיה של 1800W.
- אנרגיה של 2000W.
- אנרגיה של 2200W.

- High-performance manufacturing capacity
- R&D capability for customization
- Professional certifications and approvals



.□□□□ □□□□ □□□□ □□□□□ □
□□□□□□ □□□ **24!**