



V26

Super comfortable experience
 Painless and permanent treatment result
 Suitable for all skin types and body areas

1. 100% 100% 100% 100%.
2. 40,000,000 , 100% 100% 100% 100% 100% 100%
3. 100% , 100% 100% , 100% , 100% .
4. 100% 100% 100% 100% .
5. 6 5.14.0 100% 100% 100% 100% .
6. 100% 100% 100% 100% , 100% 100% 100%



TEC 24

One minute cooling -21°C



Best **TEC Cooling** system hair remover laser



- 1) 10 .
2) 35*12 / 20*12
3) .
4) .
5) 350 .



1 minute
and you're done

35mm {

FASTER

□□□ □□□□



.000000 00000 00000 ,0000 14 .1 0000 000 0000
 .00000000 0000 00000 6 ,0000 00000 ,00000/0000 .2
 .0000000 00 00 0000 ,0000 00000000 6 .3
 00000000 000000 .4 OEM 000000/000000) 000000...)

000000 00 00 16 ,00 12 ,00 10 ,00 8 ,0000 0"0000/00000000

0000 000000 755nm 808nm 1064nm/ 808 00nm 0000

00000000000000 0-150J/cm2

00000000 1-10 0000

00000 00000 40-800ms

0000 LCD 0000000000 0000 0000 LCD 14.0 TFT True Color

000000 00000000 000000000 0000000000 0000000000 00 0000 00000 000000 000000 00000 0000

00000000 4000W

00000 00000 220V/50HZ 110 00V/60HZ

N.W/ G.W 62 00" 78/00"

Standardized production



Professional Production R & D Sales Department



Mass production of various styles



- >>OEM your own machine body.
- >>OEM your own program software.
- >>OEM pretty machine colors.
- >>Print your LOGO on machine body and screen.

Custom Section


CASE design



LOGO design



SYSTEM design



CERTIFICATE DISPLAY

