

NEW PRODUCT

*D10*

# Portable Hair Removal Machine

-Convenient and efficient hair removal-



100000 1000000 1000000 1000 1000 100000  
100000 100000 100000 1064 808 755 1000000 ipl 10000 10000 100000

# Product details

Ultra-thin large screen, cool light strip



## 产品特点

屏幕 15/英寸 10 英寸超薄 屏 屏"超薄 超薄超薄 超薄 屏 \*

.超薄 超薄 超薄超薄 超薄 屏 屏屏 3-屏 屏屏 ,超薄超薄 超薄超薄 50-屏 屏屏 \*



1064 屏屏 3 \*nm 808nm 755nm, 屏屏 屏屏 屏屏 1-屏 3-屏 屏屏屏屏 屏屏

# Working Principle

Suits for all skin and hair types



  
**12\*20nm**  
755nm Laser  
808nm Laser  
1064nm Laser



- **755nm for white skin** (fine, golden hair removal )
- **808nm for yellow neutral skin** (brown hair removal)
- **1064nm for black skin** (black hair removal)

□□□□□□ □□□□□□

## Mini Portable

The net weight of the handle is  
about equal to one iPhone

**285g**



Ergonomic handle  
It's not tiring to take off

### 規格 仕様

1200W/1800W 有線電源 充電式電源 両方対応

幅 36\*12 mm 高さ 24\*12 mm 重量 285g

\*285gは本体の重量であり、充電式電源、有線電源、充電式電源

\*充電式電源、(充電式電源)は充電式電源、充電式電源、充電式電源、充電式電源

充電式電源、充電式電源、充電式電源、充電式電源、充電式電源

# What can **we do** in **1 MINUTE**

Time for a cup of instant coffee,  
the handle can quickly frost.





800/1000/1200/1600W

**50 Million Shots**

**USA / Germany Imported Laser Bar**

**755nm+808nm+1064nm**



**ALEX 755nm**

**For white skin**

(fine, golden hair removal )



**SPEED 810nm**

**For yellow neutral skin**

(brown hair removal)




**YAG 1064nm**

**For black skin**

(black hair removal)

**7558081064nm, 0000 0000 000 00000000 0000 000000 000000**




Before



After



Before



After




Before



After



Before



After

## Product parameters



Device Name	Diode Laser Machine
Model Number	Diode Laser D10
Wavelength	755+808+1064nm Technology
Screen size	12inch 4K-HD screen
Lifetime	50 Million shots
Pulse Duration	10-300ms
Laser Bar	100w for each one America Coherent Laser Bar
Frequency	1-10hz
Spot size	12x20mm Spot Size
Energy	1-150J
Cooling System	TEC cooling circulation
Power Of Machine	2500W
Voltage	AC220V 50HZ/60HZ
Demension of machine	380mm*460mm*300mm
Package	Aluminum box
Warranty	2 years for machine 1 year for handle

# Packing

safe and thoughtful packaging service



## Built-in prevention Collision bubble

Two-year warranty for machine handle as consumable, one-year warranty.

**OEM&ODM service for distributor.**

## Tight packaging

Training: (Video+Manual+Online Service)  
Can Keep You Operate It Easily.



## 3-5 business days delivery

Professional guide:  
24 Hours Professional online customer service,

! 24\*7 24\*7 24\*7  
24\*7 24\*7!