



EXFU VIOLIN Portable Hair Removal Laser



Simple • Safe • Enjoy
Redefine hair removal equipment



one-button start



Ice hair removal



super power



40million shine

□□□□□□ □□□□

Ingenious details I am better than others

Product detail
layout



Surround light strip

Cool lighting effect
not dazzling



Newest design handle 0.31kg

One minute cooling
Customizable glowing logo



One-of-a-kind styling

Ingenious production
focus on details



□□□□ □□□□

1200W/1800W □□□□□□ □□□□□□ □□□□ □□□□

□"□ 36*12 □□ 24*12 □□□□□□ □□□□□□

*285 □□□□□□ □□□□□□ □□□□□□ □□□□□□ ,□□□□□ □□ ,□□□□□□ □□□□ □□□□

* □□□□ □□□□□□ ,(□□□□□□□□ □□□□□□ □□□□) □□□□□□ □□□□ □□ □□ □□□□□□ □□□□ ,□□□□□□ □□□□□□ □□

□□□□□□ □□□□□□ □□□□□□ □□□□□□ □□□□□□ ,□□□□ □□ □□□□□ □□□□□□



Two colors, two spot sizes are optional



Suitable for any unwanted hair on areas like face, arms, armpits, chest, back, bikini, legs...

7558081064nm, 755nm 808nm 1064nm, 755nm 808nm 1064nm




ALEX 755nm
For white skin
 (fine, golden hair removal)



SPEED 810nm
For yellow neutral skin
 (brown hair removal)



YAG 1064nm
For black skin
 (black hair removal)



Exfu
 800 , 12----8 , W----1200W
 4 ' 14 K
 808nm 755 nm 808nm 1064nm
 50
 10~150 j/cm2,
 1-10HZ
 TEC

3500W
12*24 36*12
110V/60HZ 220 V/50HZ

1064 808 755 nm

nm

808 nm

808 nm

808 nm

! 24*7
!