



NEW

Portable Diode Laser



Mini Portable

The net weight of the handle is
about equal to one iphone

285g

Ergonomic handle
It's not tiring to take off



1200W/1800W

1200W/1800W 1200W/1800W 1200W/1800W

36*12 24*12 36*12 24*12

*285 285 285 285 285 285 285 285


* 285 285 285 285 285 285 285 285

EXFU

Exfu Violin

One-of-a-kind styling
Build your own hair removal machine

One minute cooling, 12x24cm²super cool area.
Newest design handle 0.31kg



EXFU 品牌 咖啡 咖啡機 咖啡杯 , 咖啡 咖啡 咖啡

What can **we do** in **1 MINUTE**

Time for a cup of instant coffee,
the handle can quickly frost.

EXFU®
Simple · Safe · Enjoy





800/1000/1200/1600W

50 Million Shots

USA / Germany Imported Laser Bar

755nm+808nm+1064nm



ALEX 755nm
For white skin
(fine, golden hair removal)






SPEED 810nm
For yellow neutral skin
(brown hair removal)



YAG 1064nm
For black skin
(black hair removal)

7558081064nm, 755nm 808nm 1064nm 755nm 808nm 1064nm 755nm 808nm 1064nm



Ingenious details I am better than others

Product detail
layout



Surround light strip

Cool lighting effect
not dazzling



Newest design handle 0.31kg

One minute cooling
Customizable glowing logo



One-of-a-kind styling

Ingenious production
focus on details



光源	Exfu
功率	800 ,12----8 ,W----1200W
波长	4 '14 K
波长	808nm 755 nm 808nm 1064nm
脉宽	50
脉宽	10~150 j/cm2,
脉宽	1-10HZ
脉宽	TEC TEC
脉宽	3500W
脉宽	12*24 36*12
脉宽	110V/60HZ 220 V/50HZ
脉宽	35
脉宽	45

!24*7 !
!