



□□□□□□

□□□□ 15/□□□□ 10 □□□□□□ □□ □□□□□□ □□□□□□ □□□□ □□ \*  
 .□□□□ □□□□ □□□□□□ □□□□ □□ □□□□ 3-□ □□□□ ,□□□□□□ □□□□□□ 50-□ □□□□ \*  
 1064 □□□□ 3 \*nm 808nm 755nm, □□□□ □□□□ □□□□ 1-□ 3-□ □□□□□□ □□□□



# EXFU VIOLIN Portable Hair Removal Laser



Simple • Safe • Enjoy  
Redefine hair removal equipment



one-button start



Ice hair removal



super power



40million shine

□□□□ □□□□

# Ingenious details I am better than others

Product detail  
layout



## Surround light strip

Cool lighting effect  
not dazzling



## Newest design handle 0.31kg

One minute cooling  
Customizable glowing logo



## One-of-a-kind styling

Ingenious production  
focus on details



1200W/1800W

36\*12 24\*12

\*285

\*



**Two colors, two spot sizes are optional**



Suitable for any unwanted hair on areas like face, arms, armpits, chest, back, bikini, legs...

7558081064nm, 755nm 808nm 1064nm, 755nm 808nm 1064nm, 755nm 808nm 1064nm




**ALEX 755nm**  
**For white skin**  
 (fine, golden hair removal )



**SPEED 810nm**  
**For yellow neutral skin**  
 (brown hair removal)



**YAG 1064nm**  
**For black skin**  
 (black hair removal)



Exfu  
 800 , 12----8 , W----1200W  
 4 ' 14 K  
 808nm 755 nm 808nm 1064nm  
 50  
 10~150 j/cm2,  
 1-10HZ

