

1000 □□ □□□□ □□□□ □□□ □□□ □□□□**W 1200** □□**W 1600** □□**W**


Best **TEC Cooling** system hair remover laser

[illegible]

Available in **black or white**



>> Italy water pump, it can keep machine working 24 hours without stop.



755nm

More powerful energy absorption by the melanin chromophore, making it ideal for the widest range of hair types and color
- especially light-colored and thin hair

808/810nm

Deep penetration of the hair follicle with high average power with high repetition rate for **fast treatment**. moderate melanin absorption level making it **safe for darker skin types**.
ideal for treating the arms, legs, cheeks and beard.

1064nm

low melanin absorption, focused solution for darker skin types. Offers the **deepest penetration** of the hair follicle, embedded hair in areas as the scalp, armpit, and pubic area.

Hair removal principle

Make Your Beauty Business More Easier



The laser selectively acts on the melanin in the hair follicle, destroying the hair-growing area




Natural hair loss, prevent regeneration, and achieve the purpose of hair removal



Hair removal also stimulates collagen regeneration, shrinks pores and makes skin firm and smooth

1. The laser energy is absorbed by the melanin in the hair follicle, which destroys the hair-growing area.
2. The hair follicle is destroyed, and the hair is removed.
3. The hair follicle is destroyed, and the hair is removed. The hair follicle is destroyed, and the hair is removed.



0000 000000
 000000
 .0000000 00 '00000 12.4 :0000 0000 (1
 .000000000 00000 6 (2
 000000 00000000 000000 0000 0000 00 0000 00000 00 00000 0000 ,00000000 0000 (3
 0000000
 0000000000 00000000 00000 0000000 0000000


RF 1200W	RF 1200W, 101000 J/cm ² , 1200W, 1200W
RF 1200W	RF 1200W, 101000 J/cm ² , 1200W, 1200W
RF 1200W	RF 1200W, 101000 J/cm ² , 1200W, 1200W
RF 1200W	RF 1200W, 101000 J/cm ² , 1200W, 1200W
Energy	10~150 j/cm ² , 10~150 j/cm ²
RF 1200W	40 ~ 800ms 10~150 j/cm ²
Frequency	1~10Hz
	TEC 1200W
	RF 1200W, 101000 J/cm ² , 1200W, 1200W
	RF 1200W, 101000 J/cm ² , 1200W, 1200W
	RF 1200W, 101000 J/cm ² , 1200W, 1200W
	12*20 35*12 35*12 35*12
	-10~3 10~150 j/cm ²
	AC220/110V, 50/60HZ

Custom Section


CASE design



LOGO design



SYSTEM design



RF 1200W


OUR TEAM

There are more than 100 members of production team in our factory.



OUR COUNTRIES

All the products are taking with CE/ISO certification ,suitable for world market ,
mainly used on North America ,
South America Europe
60, 000+ Customers Business development
in 102+ countries...



Weifang Mingliang Electronics Co., Ltd (公司简称:MLKJ) 为 中国 电子 行业 领先 企业 之一。公司 拥有 丰富 的 行业 经验 和 技术 实力， 提供 各种 电子 产品 和 服务。 公司 产品 包括 各种 电子 元件、 模块、 系统 等。 公司 产品 广泛应用于 工业、 商业、 民用 等领域。 公司 产品 质量 可靠， 性能 稳定， 价格 合理。 公司 产品 远销 海外， 深受 客户 欢迎。 公司 产品 符合 国家 标准， 通过 了 各种 认证。 公司 产品 具有 以下 特点：

1-□.Weifang Mingliangkj electronics Co., Ltd (□□□□ □□□□:MLKJ) □□□□ □□□□□□ □□□□ 13 □□
□□□□□□ □□□□□□ □□□□ □□□□ □□□□ □□□□ .2

□□□□□ □□□□□ □□□□□ □□□□□ □□□□□ ,□□□□□ □□□□ □□□□□ .3.

PACKING

safe and thoughtful packaging service



Built-in prevention
collision bubble

Two- year warranty for machine
handle as consumable,
one-year warranty

Tight packaging

Training:
(video +manual+online service)
can keep you operate it easily



3-5 business days
delivery

professional guide:
24 hours professional online
customer service