



1. 100% 100% 100% 100%.
2. 100% 100% 100% 100% 40,000,000 ,100% 100% 100% 100% 100% 100%
3. 100% ,100% 100% ,100% ,100% ,100% .
4. 100% 100% 100% 100% .
5. 100% 100% 6 100% '100% 5.14.0 100% 100% 100% 100% .
6. 100% 100% 100% 100% 100% ,100% 100% 100% 100%



□□□□□ □□□□□ TEC □□□□□□ □□□□□ □□□□□ □□□□ □□□ □□ □□ □□□□ □□□□ □□□□□ □□□□□□□□.

24 00000 00000 00000 00000.0000 0000.00000 0000!

- 1) 10 .பெண்கள் மற்றும் 10-40 ,பெண்கள் 16 /பெண்கள் 12 /பெண்கள் .பெண்கள் மற்றும் பெண்கள் 35*12 / பெண்கள் 20*12 பெண்கள் மற்றும் (2 பெண்கள் மற்றும் பெண்கள் ,பெண்கள் மற்றும் பெண்கள் பெண்கள் (3.
- 4) பெண்கள் மற்றும் பெண்கள் பெண்கள் மற்றும் பெண்கள் பெண்கள் .
- 5) பெண்கள் மற்றும் பெண்கள் 350 பெண்கள் மற்றும் பெண்கள் .

1 minute
and you're done

35mm {

FASTER

1. 14.1

2. 6, 8, 10, 12, 14, 16

3. 6, 8, 10, 12, 14, 16

4. OEM (OEM/ODM) (OEM/ODM...)

5. 16, 12, 10, 8, 6, 4, 2, 1

6. 755nm 808nm 1064nm/ 808 nm

7. 0-150J/cm2

8. 1-10

9. 40-800ms

10. LCD 14.0 TFT True Color

11. 4000W

12. 220V/50HZ 110 V/60HZ

13. N.W/ G.W

14. 62 78/

15. 62 78/


Company Strength



- >>OEM your own machine body.
- >>OEM your own program software.
- >>OEM pretty machine colors.
- >>Print your LOGO on machine body and screen.

Custom Section


CASE design



LOGO design



SYSTEM design



□□□□□ □□□□□

CERTIFICATE DISPLAY



Packing

safe and thoughtful packaging service



Built-in prevention Collision bubble

Two-year warranty for machine handle as consumable,
one-year warranty.

OEM&ODM service for distributor.

Tight packaging

Training: (Video+Manual+Online Service)
Can Keep You Operate It Easily.



3-5 business days delivery

Professional guide:
24 Hours Professional online customer service,

