



00 000 CE Medical, ISO13485, 00000000  
 0000 000000 ,00000000 0000000.  
 0000000 00 0000 0000 0000 0000000 000000 0000 0000 00000000 0000.  
 000000 00000000 0000 000000 000000.  
 00000000 000 00000 000000 000000.  
 00000000 0000 0000.  
 0 000000 ,000000 000000000 0000000 000000-YouTube 000000000.



**1000** 1000mm 1000mm 1000mm 1000mm **W 1200** 1200mm **W 1600** 1600mm

## Best **TEC Cooling** system hair remover laser

[illegible]

Available in **black or white**



>> Italy water pump, it can keep machine working 24 hours without stop.




|           |                                                     |
|-----------|-----------------------------------------------------|
| RF 1200W  | RF 1200W, 101000 J/cm <sup>2</sup> , 1200W, 1200W   |
| RF 1200W  | RF 1200W, 101000 J/cm <sup>2</sup> , 1200W, 1200W   |
| RF 1200W  | RF 1200W, 101000 J/cm <sup>2</sup> , 1200W, 1200W   |
| RF 1200W  | RF 1200W, 101000 J/cm <sup>2</sup> , 1200W, 1200W   |
| Energy    | 10~150 j/cm <sup>2</sup> , 10~150 j/cm <sup>2</sup> |
| RF 1200W  | 40 ~ 800ms 10~150 j/cm <sup>2</sup>                 |
| Frequency | 1~10Hz                                              |
|           | TEC 1200W                                           |
|           | RF 1200W, 101000 J/cm <sup>2</sup> , 1200W, 1200W   |
|           | RF 1200W, 101000 J/cm <sup>2</sup> , 1200W, 1200W   |
|           | RF 1200W, 101000 J/cm <sup>2</sup> , 1200W, 1200W   |
|           | 12*20 35*12 35*12 35*12                             |
|           | -10~3 10~150 j/cm <sup>2</sup>                      |
|           | AC220/110V, 50/60HZ                                 |

## Custom Section


### CASE dedign



### LOGO design



### SYSTEM design



RF 1200W


## OUR TEAM

There are more than 100 members of production team in our factory.



## OUR COUNTRIES

All the products are taking with CE/ISO certification ,suitable for world market ,  
mainly used on North America ,  
South America Europe  
60, 000+ Customers Business development  
in 102+ countries...



The collage consists of 12 individual photographs arranged in three rows of four. The top row shows group portraits of team members, some giving thumbs up. The middle and bottom rows show medical professionals in white coats examining patients, using medical equipment, and interacting with local staff and patients in various settings, including clinics and outdoors.

1-□.Weifang Mingliangkj electronics Co., Ltd (□□□□ □□□□:MLKJ) □□□□ □□□□□□ □□□□ 15 □□  
□□□□□□ □□□□ □□□□□□ □□□□ □□□□ □□□□ □□ □□ .2  
□□□□□□ □□□□ □□□□□□ □□□□□□ □□□□□□ ,□□□□□□ □□□□ □□□□□□ .3.

# PACKING

safe and thoughtful packaging service



Built-in prevention  
collision bubble

Two- year warranty for machine  
handle as consumable,  
one-year warranty

Tight packaging

Training:  
(video +manual+online service)  
can keep you operate it easily



3-5 business days  
delivery

professional guide:  
24 hours professional online  
customer service