

1000 □□ □□□□ □□□□ □□□ □□□ □□□□**W 1200** □□**W 1600** □□**W**


Best **TEC Cooling** system hair remover laser

[illegible]

Available in **black or white**



>> Italy water pump, it can keep machine working 24 hours without stop.



755nm

More powerful energy absorption by the melanin chromophore, making it ideal for the widest range of hair types and color
- especially light-colored and thin hair

808/810nm

Deep penetration of the hair follicle with high average power with high repetition rate for **fast treatment**. moderate melanin absorption level making it **safe for darker skin types**. ideal for treating the arms, legs, cheeks and beard.

1064nm

low melanin absorption, focused solution for darker skin types. Offers the **deepest penetration** of the hair follicle, embedded hair in areas as the scalp, armpit, and pubic area.

Hair removal principle

Make Your Beauty Business More Easier



The laser selectively acts on the melanin in the hair follicle, destroying the hair-growing area



Natural hair loss, prevent regeneration, and achieve the purpose of hair removal



Hair removal also stimulates collagen regeneration, shrinks pores and makes skin firm and smooth

1. The laser energy is absorbed by the melanin in the hair shaft, which is the main component of the hair. The energy is converted into heat, which destroys the hair follicle and prevents the hair from regrowing.

2. The laser energy also stimulates the production of collagen in the skin, which helps to shrink the pores and make the skin smoother and firmer.

3. The laser energy also destroys the sebaceous glands, which are the glands that produce oil for the hair. This helps to prevent the hair from regrowing and also helps to reduce the risk of acne.



0000 000000

00000000 00000000 00000 0000000 0000000 00 0000

.00000000 00 '00000 12.4 :0000 0000 (1

.000000000 00000 6 (2

000000 00000000 0000000 0000 0000 00 0000 0000 00 00000 0000 ,00000000 0000 (3

0000000

0000000000 00000000 00000 0000000 0000000


RF 1200W	RF 1200W, 101000 J/cm ² , 1200W, 1200W
RF 1200W	RF 1200W, 101000 J/cm ² , 1200W, 1200W
RF 1200W	RF 1200W, 101000 J/cm ² , 1200W, 1200W
RF 1200W	RF 1200W, 101000 J/cm ² , 1200W, 1200W
Energy	10~150 j/cm ² , 10~150 j/cm ²
RF 1200W	40 ~ 800ms 10~150 j/cm ²
Frequency	1~10Hz
	TEC 1200W
	RF 1200W, 101000 J/cm ² , 1200W, 1200W
	RF 1200W, 101000 J/cm ² , 1200W, 1200W
	RF 1200W, 101000 J/cm ² , 1200W, 1200W
	12*20 35*12 35*12
	-10~3 10~150 j/cm ²
	AC220/110V, 50/60HZ

Custom Section


CASE design



LOGO design



SYSTEM design



RF 1200W



公司 mingliangkj:

Weifang Mingliang Electronics Co., Ltd (公司简称:MLKJ) 公司主要从事 电子产品 的研发 生产 销售 服务 等业务 , 公司 拥有 先进 的生产 设备 , 完善 的质量 管理体系 , 产品 远销 欧美 日韩 等 地区 , 深受 客户 的 好评 . 公司 秉承 “ 以人为本 , 科技 领先 ” 的经营理念 , 为客户提供 优质的 产品和服务 . 公司 地址 : 山东省 潍坊市 潍城区 东风 街 100 号 . 公司 电话 : 0536-2611111 . 公司 网站 : www.mingliangkj.com .

□ □□□□ ,□□□□□□

□□□□□□□ □□ □□□□□□ □□□□□□ □□ □□□□□□□ ,□□□□□ □□□□□□□ □□□□ 13 □□ □□□□ □□□□□□ .□□□□□ □□.

□□□□ □□□□□

1-□.Weifang Mingliangkj electronics Co., Ltd (□□□□□□ □□□□:MLKJ) □□□□□□ □□□□□□□ □□□□ 15 □□

□□□□□□ □□□□□ □□□□□□ □□□□ □□□□□ □□□ □□ .2

□□□□□□ □□□□□ □□□□□□ □□□□□ □□□□□□ ,□□□□□□ □□□□ □□□□□□ .3.

PACKING

safe and thoughtful packaging seivice



Built-in prevention
collision bubble

Two- year warranty for machine
handle as consumable,
one-year warranty

Tight packaging

Training:
(video +manual+online service)
can keep you operate it easily



3-5 business days
delivery

professional guide:
24 hours professional online
customer service