

DIODE LASER hair removal machine

■ 2 Years Warranty ■ OEM / ODM Service ■ 3 waves 1064nm +808nm + 755nm



DIODE LASER hair removal machine D10

* 12—8 treatment sessions per area.

* 3-5 sessions per area, 50-60% hair reduction.

* 3 1064nm 808nm 755nm, 1-3 sessions per area

Handle Display

Two colors, two spot sizes are optional



755 : 755nm 808nm 1064nm

755nm 755nm 808nm 1064nm 755nm.

808nm 808nm 755nm 1064nm 808nm.

1064nm 1064nm 755nm 808nm 1064nm.

Working Principle

755nm and 808nm and 1064nm , suits for all skin and hair types.



ALEX 755nm

For white skin

(fine, golden hair removal)



SPEED 810nm

For yellow neutral skin

(brown hair removal)



YAG 1064nm

For black skin

(black hair removal)

The real experience is visible

Through live test verification ,safe ,long,painless
and effective



1) .14 14 :
(2) :
(3 OEM: , , .



Product details

Ultra-thin large screen, cool light strip



!00000 000000 000 ,000000 000000
00000000 0000 24!