



0000 0000000 000000 000000 00000 000
 0000 00000 (1 TEC, 0000000 00000 0000 24 ,000 00 00000
 2) 1200 0000 0000w/1800w, 000 0000 0000 0000 ,0000 000000
 000000 00 000000 000000 (3
 000 0000000 0000 ,00000 000 0000 0000 (4
 0000000 0000 000 000000 ,0000000 0000 00000 00000 0000 (5

Safe • Fast • Painless • permanent

Safe • Fast • Painless • permanent



*. □□□□ □□□□ □□□□□ □□□□ □□□□ □□□□ □□□□ □□□□ □□□□□□□□.

**ULTRA-LOW
Temperature
-31°C**

Ultra low temperature
protect skin
not burned by the laser



Three Simultaneous Wavelengths in one Applicator

12mm*20mm / 12mm*35



=



Alex
755nm

+



Speed
808nm

+



YAG
1064nm

Mix Laser 755nm+808nm+1064nm
Multiple Laser Wavelengths and Technologies

Ideal for range
of hair colors

Safe for darker
skin types

Perfect solution
for darker skin

LASER COMPARISON

【Other - Lasers】



- ✓ The original structure is not light enough.
- ✓ Big size.
- ✓ Short life.

【2022-MLKJ-Lasers】



- ♥ Lighter weight.
- ♥ Smaller size.
- ♥ More advanced structure design.
- ♥ More advanced performance.

【2022-MLKJ-Medical-Lasers】



- ♣ More advanced packaging technology.
- ♣ Higher energy densit.
- ♣ Lighter appearance.
- ♣ Longer life.

□□□□ □□□□







1064nm (carbon dioxide laser) is used for skin resurfacing and tightening.
755nm (alexandrite laser) is used for hair removal and skin rejuvenation.
808nm (diode laser) is used for hair removal and skin rejuvenation.
1064nm (carbon dioxide laser) is used for skin resurfacing and tightening.
The treatment is performed in a clinical setting with a professional wearing protective eyewear and gloves.



Before

After



腋下腋毛脫除

---- 腋下腋毛脫除,腋下腋毛,'腋下腋毛 14 腋下腋毛

---- 腋下腋毛 6,腋下腋毛 6,腋下腋毛 腋下腋毛

----6 腋下腋毛 腋下腋毛 腋下腋毛 腋下腋毛,腋下腋毛 腋下腋毛

---- 腋下腋毛,腋下腋毛,腋下腋毛:腋下腋毛 腋下腋毛 腋下腋毛.....

腋下腋毛 腋下腋毛

腋下腋毛 808 腋下腋毛 腋下腋毛 腋下腋毛 腋下腋毛

腋下腋毛 755nm/808nm/1064nm

腋下腋毛 10"腋下腋毛/腋下腋毛 腋下腋毛,腋下腋毛 16/腋下腋毛 12/腋下腋毛

腋下腋毛 腋下腋毛

腋下腋毛 腋下腋毛 腋下腋毛 14.0 腋下腋毛 腋下腋毛 腋下腋毛 腋下腋毛'

腋下腋毛 腋下腋毛 腋下腋毛 10-40 腋下腋毛 腋下腋毛

腋下腋毛 腋下腋毛 10~150 j/cm2, 腋下腋毛

腋下腋毛 腋下腋毛 40 ~ 800ms 腋下腋毛

腋下腋毛 1~10Hz

腋下腋毛 腋下腋毛 -5~3 腋下腋毛 腋下腋毛

G.W., 腋下腋毛 腋下腋毛 80 腋下腋毛 61*59*115 ,腋下腋毛

1

Medical CE TUV ISO certification and more Complete certification materials



**Standardized
production**



**Professional
Production R & D
Sales Department**



**Mass production
of various styles**



Packing

safe and thoughtful packaging service



Built-in prevention Collision bubble

Two-year warranty for machine handle as consumable,
one-year warranty.

OEM&ODM service for distributor.

Tight packaging

Training: (Video+Manual+Online Service)
Can Keep You Operate It Easily.



3-5 business days delivery

Professional guide:
24 Hours Professional online customer service,

! 00000 00 000000 00000 0000 000000
7 00000 000000X24 0000!