



DIODE LASER

STRONGER SMARTER FASTER

SUPER ICE PAINLESS EXPERIENCE
PERMANENT HAIR REMOVAL
COMFORTABLE HAIR REMOVAL

Rapid cooling, only 30s

1 minute hair removal




ALEX 755nm
For white skin
 (fine, golden hair removal)



SPEED 810nm
For yellow neutral skin
 (brown hair removal)



YAG 1064nm
For black skin
 (black hair removal)



755nm .(fine/golden hair removal) For white skin
 808nm .(brown hair removal) For yellow neutral skin
 1064nm (black hair removal) For black skin

Applicable to all treatment sites



本產品 適用於 各種部位 **ICE PLUS**。適用於 各種 皮膚類型 及 膚色。
每星期 24 小時 隨時隨地 隨手 隨心 隨地。



Just One minute!
Quick cooling down to **-25°C**

[illegible]

BEFORE AND AFTER TREATMENT

MAKE YOUR SKIN SILKY AND FULL OF CHARM!





000000 000000
 0000 000 , '0000 14 00000 0000 000
 0000 000000 000000 000 0000 6 , 000 0000 6 , 000000 000 .2
 000 000 000 00 000000 0000 , 000 000000000 6 .3
 0000000 000000 .4 OEM 000/000000/00000/000) 000000...)




--	--	--	--	--	--	--	--

光源	超連続光源 D18
光源の寿命	約 16~8 万時間 (連続運転時)
出力	4 W (連続) 14 W (パルス) 最大
波長	808nm 755 nm 808nm 1064nm
光束径	40 mm (最大)
照射密度	10~150 J/cm ² (連続運転時)
照射周波数	1-10Hz
冷却方式	水冷式 (TEC 冷却) 冷却水温度 10℃ 以下 (冷却水流量 10 L/min 以上)
消費電力	3500W

12*20 35*12/ 110V/60HZ 220 V/50HZ

MACHINE INTRODUCTION





██████ **FDA**, ██████████ ████████

1 00000 0000000 00000000 0000 000000 00000000 000000 000000 00 0000 000 ,0000 **5** 0000 0000000 0000!

□ □□□□ □□□□□ □□□□□ □□□□□ □□□□□□□□□□-**FDA & CE** □□□□ □□□□□ □□□□□ □□□□□

□□□□□□□□□
□□□□□□□□□□ □□□□ *
□□□□□□ □□□□□ *
□□□□□ □□□□□ □□□□ *
□□□□□□□□ □□□□□□□ □□□□□ *

□□□□□□□□
(□□□□□□ □□ □□□□□□ □□□□) □□□□□□ □□□□ □□□□ ,□□□□□□□ □□□□□□□ :□□□□□□□ *
.□□□□ □□ □□□□□□ □□□□ □□□□□□□ □□□□ □□□□□□ *
□□□□□□ * OEM

□□□□□□□ □□□□ □□□□□ □□□□ 3-7 :□□□□□□□ □□□□

□□□□□□□ :□□□□□□□ □□□□, DHL, TNT, Fedex □□□□□□□ □□□□□ □□□□
□□□□□□□□ □□□□□□ □□□□□□□ :□□□□□□□ □□□□□
□□□□□ □□□□ □□□□□□□ □□□□□ □□□□□ □□□□□ ,□□□□□□□ :□□□□□□□ □□□□□
□□□□□□□□□ □□□□□ **24*7** !□□□□□□□□ □□□□□□□□□□ ,□□□□ □□□□□ □□□□□□□!