



# V26

Super comfortable experience  
Painless and permanent treatment result  
Suitable for all skin types and body areas

1. 100% 100% 100% 100%.
2. 40,000,000 ,
3. , , ,
- 4.
5. 6 5.14.0
6. , .

TEC .  
 24 .



One minute cooling -21°C

## Best TEC Cooling system hair remover laser

- 1) 10-40 , 16 / 12 /
- 2) 35\*12 / 20\*12

3. 100% 100% 100% , 100% 100% 100% 100% (3.

4) 100% 100% 100% 100% 100% 100%.

5) 100% 100% 350 100% 100% 100%.

**1 minute**  
and you're done

35mm

**FASTER**

100% 100%

. 100% 100% 100% , 100% 14 .1 100% 100% 100%

. 100% 100% 100% 6 , 100% 100% , 100%/100% .2

. 100% 100% 100% 6 .3

100% 100% .4 OEM 100%/100% 100%...)

100% 100% 100% 16 , 100% 12 , 100% 10 , 100% 8 , 100% 100%/100%

100% 100% 755nm 808nm 1064nm/ 808 100nm 100%

100% 100% 0-150J/cm2

100% 100% 1-10 100%

100% 100% 40-800ms

100% LCD 100% 100% LCD 14.0 TFT True Color

100% 100% 100% 100% 100% 100% 100% 100% 100% 100% 100% 100%

100% 100% 4000W

100% 100% 220V/50HZ 110 100V/60HZ

**Standardized production**



**Professional Production R & D Sales Department**




**Mass production of various styles**



- >>OEM your own machine body.
- >>OEM your own program software.
- >>OEM pretty machine colors.
- >>Print your LOGO on machine body and screen.

## Custom Section


**CASE** design



**LOGO** design



**SYSTEM** design



□□□□ □□□□

# CERTIFICATE DISPLAY

