

New arrivals

EXFU

SIMPLE . SAFE . ENJOY

New experience of hair removal



EXFU Hair Removal Machine is a safe and effective way to remove unwanted hair. It uses a combination of 1064nm, 808nm, and 755nm wavelengths to target hair follicles and prevent regrowth. The device is FDA-approved and has a track record of over 10 years.

**FDA**

EXFU

EXFU has been used by over 15 million people in over 100 countries. It is a safe and effective way to remove unwanted hair. \*

.EXFU is a safe and effective way to remove unwanted hair. It uses a combination of 1064nm, 808nm, and 755nm wavelengths to target hair follicles and prevent regrowth. \*

1064nm, 808nm, 755nm, EXFU is a safe and effective way to remove unwanted hair. It uses a combination of 1064nm, 808nm, and 755nm wavelengths to target hair follicles and prevent regrowth. 1-3 months of treatment.



# EXFU VIOLIN Portable Hair Removal Laser



Simple • Safe • Enjoy  
Redefine hair removal equipment



one-button start



Ice hair removal



super power



40million shine

□□□□□ □□□□

# Ingenious details I am better than others

Product detail  
layout



## Surround light strip

Cool lighting effect  
not dazzling



## Newest design handle 0.31kg

One minute cooling  
Customizable glowing logo



## One-of-a-kind styling

Ingenious production  
focus on details



□□□□ □□□□

1200W/1800W □□□□□□ □□□□□□ □□□□ □□□□

□"□ 36\*12 □□ 24\*12 □□□□□□ □□□□□□

\*285 □□□□□□ □□□□□□ □□□□□□ □□□□□□ ,□□□□□ □□ ,□□□□□□ □□□□ □□□□

\* □□□□ □□□□□□ ,(□□□□□□□□ □□□□□□ □□□□) □□□□□□ □□□□ □□ □□ □□□□□□ □□□□ ,□□□□□□ □□□□□□ □□

□□□□□□ □□□□ □□□□ □□□□□□ □□□□□□ ,□□□□ □□ □□□□□ □□□□□□



**Two colors, two spot sizes are optional**



Suitable for any unwanted hair on areas like face, arms, armpits, chest, back, bikini, legs...

7558081064nm, 755nm 808nm 1064nm, 755nm 808nm 1064nm




**ALEX 755nm**  
**For white skin**  
 (fine, golden hair removal )



**SPEED 810nm**  
**For yellow neutral skin**  
 (brown hair removal)



**YAG 1064nm**  
**For black skin**  
 (black hair removal)



Exfu  
 800 , 12----8 , 1200W  
 4 ' 14 K  
 808nm 755 nm 808nm 1064nm  
 50  
 10~150 j/cm2,  
 1-10HZ  
 TEC

3500W  
12\*24 36\*12  
110V/60HZ 220 V/50HZ

1064 808 755

808 nm

808 nm

808 nm

**! 24\*7**  
**!**