



808+ND

Diode laser hair removal
 ND YAG laser tattoo removal

808nm Nd yag

1. 1064nm Nd yag , Nd yag laser hair removal 1-2 times
2. 1064nm Nd yag , Nd yag laser tattoo removal : Nd yag laser tattoo removal 10-40 times
3. Nd yag: 1064nm Nd yag , Nd yag laser hair removal 5 times/532nm, 1064nm Nd yag/532nm, 1320nm Nd yag.







□□□□ □□□□

Three wavelengths work together

12*20mm² {



12*35mm² {



Suitable for hair removal on any part of the body,
Such as arms, legs, face, armpits, back, chest, etc.



7558081064 000000 0000 0000 000 0000000 000000 0000000.
000000 0000000 20-40 00 0000 .000000 00 000000.




Before

After



Before



After



Before



After

5 therapeutic **Heads**

- 532 & 1064: removing tattoo, eyeliner and lip line
- 1320: black-faced doll whitening and whitening skin
- Adjustable 532 & 1064: removing large-area tattoos



Adjustable
532nm



Adjustable
1064nm



Black doll
1320nm



Fixed
532nm




Fixed
1064nm

□□ □□□□□□ □□□□ Nd yag:


1064 □□□□□□□□ ,□□□□□□ □□□□ 5 □□□□nm/532nm, 1064 □□□□nm/532nm, 1320 □□□□nm.

Working Principle



1. 0000000 000 0000 6 ,000 0000 ,0000/000.
2. 000 000 0000000000.
3. 000000 000000 OEM 00000/00000) 000000...)

System Design



808 Mode:Operation interface

Laser Mode:Tattoo removal

系统名称	808 激光脱毛机
系统组成	808 激光 Nd yag, 808 冷却系统
系统功率	2000W
系统 SHR	1-10HZ
808 激光 尺寸	12*20 英寸 35*12 英寸
冷却系统 Nd yag	冷却系统 5 英寸 英寸 ,冷却系统 冷却系统
冷却系统 功率	10-50 J/cm2
冷却系统 速度	1-10 冷却系统 冷却系统
冷却系统 温度	-21
冷却系统 冷却系统	冷却系统 冷却系统 冷却系统 冷却系统 冷却系统 冷却系统 冷却系统 冷却系统 冷却系统 冷却系统
冷却系统 冷却系统	冷却系统 LCD 冷却系统 冷却系统 TFT 12 英寸'
冷却系统	220v/50hz 110 英寸v/60hz
冷却系统 冷却系统	116*60*61 英寸
冷却系统 冷却系统	90 英寸



15 Years Laser Beauty Device Manufacturer


Make your beauty business easier



1. Weifang Sunshinekj electronics Co., Ltd (公司简称: MLKJ) 是一家专业从事美容激光设备研发、生产和销售的高新技术企业。公司成立于2008年，拥有15年R&D经验，专注于为客户提供高品质的激光美容设备。公司占地面积20000平方米，拥有先进的生产设备和完善的质量管理体系。产品广泛应用于美容院、医疗美容机构等。公司秉承“诚信、创新、服务”的经营理念，致力于为全球客户提供优质的产品和服务。

Premium OEM Factories

High-performance manufacturing capacity
R&D capability for customization
Professional certifications and approvals



Packing


Safe and thoughtful packaging service



Tight packaging

The machine shall be made of waterproof materials and packaged

**Anti collision foam board
inside aluminum box**



3-5 business days delivery

Professional guide:

24 Hours Professional online customer service