



40K CAVITATION 5IN1

RF+VACUUM+CAVITATION
+LASER PADS SLIMMING MACHING

START



Advantage^e



Advantage

- **portable**

5 in 1 salon beauty system
saving shipping cost

5 handles

for slimming, skin tightening, wrinkle removal

- **Advantage**

high power cavitation 300W more effective

vacuum head help a lot for supus fat cell

2 years warranty

multi-color for option





Cavitation

Frequency:4Mhz

Power:150W

Burning explode fat cell



Monopolar RF

Frequency:40khz

Power:300W

Body shape fat reduction



Big tripolar RF

Frequency:4Mhz

Power:150W

Skin tightening lifting wrinkle removal



Small Tripolar RF

Frequency:1Mhz

Power:150W

Skin tightening lifting wrinkle removal



Vacuum

Frequency:1MHz

Pressure:-90kpa

Slimming Remove surplus fat cell

8寸 TFT LCD
触摸屏

RF 8 寸 TFT LCD
CavitationVacuumRF (Cavitation RF+Vacuum RF)

触摸屏

触摸屏 rf 触摸屏
触摸屏
RF 触摸屏
RF 触摸屏) 触摸屏)
RF 触摸屏) 触摸屏)

触摸屏
触摸屏
触摸屏 cavitation

40 触摸屏-触摸屏
300 触摸屏

RF 1-10 MHZ () 150 ()
 RF 1-10 MHZ () 150 ()
 100 KPA
 38*31*47 :
 46*43*54 :
 220V AC / 110V AC
 N.W. 15
 G.W. 25

Treatment before & after compare




：

- >Suitable for 6 different color skin,including the dark skin.
- >The sapphire temperature cools down 0~3°C,clients feel comfortable and painless in whole treatment .
- >Long continuous working time,ensure the works in Clinic/salon use.

AMAZING EFFECT

Before & After



Before


Five weeks later

Eight weeks later



Before

After



Before

After



Before

After



Before

After

Free logo service



□□□ □□□□□□□!