

Diode Laser



15 Bar **1800W** Handle

*Increase the treatment head of nasal hair
and treat small parts easily



.000000 000000 0000 000000 000000
;000 00 000 000 000000 .0000000000 0000*
;000 00 000 000 000000 *
.000000 00000 *
;00000 000000000 0000000000 00000 00000 *
808 0000000000 00000000 00 00000 *nm 7558081064 00nm;

350g
Ultra light handle



12×36mm

Handle

1800W diode laser hair removal



12×24 mm

Handle

1200W diode laser hair removal


Three Waves 755 nm 808nm 1064nm, 755nm 808nm 1064nm, 755nm 808nm 1064nm, 755nm 808nm 1064nm.

755nm .(Alex) 755nm 808nm 1064nm

808nm .(Speed) 755nm 808nm 1064nm

1064nm .(YAG) 755nm 808nm 1064nm

755nm 808nm 1064nm 755nm 808nm 1064nm 755nm 808nm 1064nm






ALEX 755nm
For white skin
(fine, golden hair removal)



SPEED 810nm
For yellow neutral skin
(brown hair removal)



YAG 1064nm
For black skin
(black hair removal)



Treatment Comparison





Emergency stop button

12 inch big screen
quick touch
easy operate

Diode laser handle

Vents

Plug