



Three wavelength

755nm 808nm 1064nm diode hair removal technologies in one handle

755nm 808nm 1064nm

755nm 808nm 1064nm 755nm 808nm 1064nm 755nm 808nm 1064nm 755nm 808nm 1064nm 755nm 808nm 1064nm

Emergency stop button

Online Customization

Applicator 12x5mm

Medical handle 350g lightweight handle

14 inch big screen quick touch easy operate

Advantage

Fast, Painless, Permanent Hair Removal

24 hours working continuously

Reduce preparation time

Increase your profit

Minute cooling

Low system noise and strong cooling effect


No need for local anesthesia

Expand your patient base

Suitable for treatment of all parts of the body

--	--	--	--	--	--	--	--

12 000000 0000x26 12 / 0"0x24 .000000 000000 000000 00 000000 000000 ,000000 0000 0"0
000000 ,000000 000000 ,000 000000 00000000 00000000 0000000000 00 000000 000000.



- spot size:12*36



- spot size:12*24



spot size:12*36



spot size:12*24



spot size:12*36




spot size:12*24

□ □ □ □ □

[illegible][illegible]

Efficacy

Perment hair removal for all skin type

Very fair Fair	755nm suitable for light skin hair removal	
Medium Olive	808nm suitable for neutral skin hair removal	
Brown Black	1064nm suitable for black skin hair removal	

Safety

Almost no skin scattering, no harm to the skin and sweat glands, no scar, no any side-effect

Refuse to repeat and leave No scum



1 week - 2 weeks
2 times a week
- 75 hair loss - Start to grow slowly - Smaller pores



3 week - 4 weeks
2 times a week
- Hair becomes thinner and less rejuvenate tender skin smooth body



5 week - 8 weeks
2 times a week
- Select according to hair growth status use it selectively, say goodbye repeated hair removal

□□□□ □□□□

□□□□□□ □□□□□ □□□□□□□ □□□□□□ □□□ □□□□□ ,□□□□□ □□ □□□□□□ □□□□□□ □□□ □□ □□□□□□□ □□□□□□.

□□□□□□ □□□□□ □□□□□ □□□□□

New upgrade system

The newscreen is clear easy to operate.



Company & Panking □□□□

MLKJ

CUSTOMER SERVICE

15 YEARS FACTORY, 2 YEARS WARRANTY, 102 COUNTRIES, 60,000+ CUSTOMERS.

MLKJ—MAKE YOUR BEAUTY BUSINESS EASIER



Packing

safe and thoughtful packaging service



Built-in prevention Collision bubble

Two-year warranty for machine handle as consumable, one-year warranty.

OEM&ODM service for distributor.

Tight packaging

Training: (Video+Manual+Online Service)
Can Keep You Operate It Easily.



3-5 business days delivery

Professional guide:
24 Hours Professional online customer service,

□□□□ □□□□□□ □□ □□□□ □□□□ □□□□ □□□ □□□ □□□□□ □□□.