

350g lightweight **handle**, more ergonomic


Available in **black or white**




High-quality
laser bars
imported from
USA

1000/1200/1600ww high power



Fast hair removal



➤ 10bar
1000W




➤ 12bar
1200W



➤ 16bar
1600W

For all skin types



755nm / 808nm / 1064 nm





14 00000 0000 00000 00000 1064 808 755 00 0000 000 000' 0000

* 0000 0000 0000 00 0000 0000000 000000 000

* 000000 000 00

* 0000 0000 000000

* 000000 000000 000 000000

The new 14-inch screen is clear
easy to operate.



OEM/ODM SEVRICE

3D LOGO with luxurious texture.