

NEW ! Technology



Free to be yourself

1 minute of painless hair removal,
Feeling the comfort and coolness that
has never been seen before.

14-inch screen

2 year warranty + work 24 hours



0000000 0000000 0000 0000 000000 00 000000

1.) 0000 0000 000 0000000 000000 0000 0000
000000 000 00000 000000 ,00000 00000 00000 0000000 (2.

1 minute
and you're done

35mm {

FASTER

1000 10,0" 20 * 12 1200 16,0" 35 * 12

1000 10,0" 20 * 12 1200 16,0" 35 * 12

1600 16,0" 35 * 12


Handle Details

Three Wavelengths Work Togher




12*20nm

755nm Laser
808nm Laser
1064nm Laser



12*35nm


755nm Laser
808nm Laser
1064nm Laser



Best **TEC Cooling** system hair remover laser



በጥንቃቄ በሰው ሕይወት ውስጥ የሚከሰቱ ችግሮች! በጣም አስተማሪና ትርጉሞች በመሆናቸው በአጭር ጊዜ ውስጥ ይታያል።



3 1000w, 1200w, 1600w
755 (808nm / 1064nm)
808nm (808nm / 1064nm)

Stuit to any color of skin



Application:

Elight for Skin Rejuvenation, Skin Tightening, Wrinkle Removal, Acne Removal, Pigment Removal, Vascular Removal, Breast Lifting, Age Spot Removal etc.

808 Hair Removal treatment pictures



Before and After

Treatment comparison



Screen Image


10.4 inch touch screen easy to operate.



1. 1.14 2. 6 3. 4. OEM (/) ...)

The new **14-inch 4K** screen

Support system customization



主要参数

波长	755nm 808nm 1064nm 三波长 可调
脉冲宽度	16 / 12 / 10 ,可调 可调
功率	50w
治疗头	14 英寸 触摸屏 治疗头
治疗头	808nm / 755nm / 1064nm
治疗头	12 * 20mm ² / 12 * 35mm ²
脉冲宽度	808 10,000,000-40,000,000 可调 :可调
脉冲宽度	10-150 J / cm ² 150 (可调) J / cm ² (可调)
脉冲宽度	40 ~ 800ms 可调
脉冲宽度	1.0-10 可调;
脉冲宽度	TEC 制冷 可调 可调
功率	1000w / 1200w / 1600w
功率	2000w
电压	220V / 50Hz 110 V / 60Hz
温度	-10 ~ 3 可调 可调
温度	27 ~ 31 可调 可调

□□□□ □□□□
□□□□ □□□□

AC220V / 110V 50 ~ 60Hz
95 □"□

□□□□ □□□□

1. Weifang Sunshinekj () " " ' : MLKJ) □□□□□□ □□□□ □□□□ □□□□ □□

□□□□□□□□ □□□□ 13 □□ ,□□□□ □□□□ □□□□□□□□

About Us

We Are 13 Years

Professional high-tech beauty equipment manufacturer in China.

潍坊明亮电子有限公司

坚守客户价值不动摇·让客户满意
This firmly to customer's value to make them feel satisfied
坚守员工价值不动摇·让员工成长
Hold Fast to employees' value to let them develop



Mingliangkj in 2007, Through 13 years ,we have built reliable Production ,Quality Control ,Warehousing and Sale&Service department.

Products around world ,including Europe ,North America, Asia and so on .more than 600 clients in more, than 100 countrys all over the world



NEW





2. 本公司 產品 均 經 R & D 團隊,
不斷 研發 , 確保 產品 品質 優良

Research and Development

We have professional Production R & D department.
From design research and development to production, every step is strictly checked to ensure product quality.



CAD and PCB drawing



Electrical schematic diagram and preparation procedures



Ammeter test



Install the motherboard



Assemble the hardware



Leave the factory after passing the inspection



Packing And Delivery

1



Print Logo



Check accessories before packing

2



Wiping and Wrapping machine



Rigorous inductive packing

3



Reminder identification



Fast delivery