



Free to be yourself

A minute of painless freezing hair removal,
Feeling the comfort and coolness that
has never been seen before.

14-inch screen

2 year warranty + work 24 hours

TEC 14-inch screen
OEM / ODM.
24 hours



2years Warranty



102 Countries

60,000+ Customers



TEC 14-inch screen

1. 808 : TEC 14-inch screen 755 TEC 14-inch screen 3 ; TEC 14-inch screen 808 TEC 14-inch screen yag 1064nm

TEC 14-inch screen TEC 14-inch screen TEC 14-inch screen , TEC 14-inch screen

TEC 14-inch screen TEC 14-inch screen , TEC 14-inch screen TEC 14-inch screen : TEC 14-inch screen .2

. TEC 14-inch screen , TEC 14-inch screen 1-10 TEC 14-inch screen : TEC 14-inch screen .3

TEC 14-inch screen TEC 14-inch screen TEC 14-inch screen : TEC 14-inch screen 12 TEC 14-inch screen .4 TEC, TEC 14-inch screen TEC 14-inch screen

. TEC 14-inch screen TEC 14-inch screen , TEC 14-inch screen TEC 14-inch screen TEC 14-inch screen TEC 14-inch screen , °C 24 TEC 14-inch screen

. TEC 14-inch screen / TEC 14-inch screen 6.5 TEC 14-inch screen TEC 14-inch screen TEC 14-inch screen : TEC 14-inch screen TEC 14-inch screen .5

, TEC 14-inch screen 7 * TEC 14-inch screen 14 TEC 14-inch screen TEC 14-inch screen TEC 14-inch screen , TEC 14-inch screen , TEC 14-inch screen TEC 14-inch screen , TEC 14-inch screen TEC 14-inch screen .6

TEC 14-inch screen TEC 14-inch screen TEC 14-inch screen .

Free to be yourself

A minute of painless freezing hair removal,
Feeling the comfort and coolness that
has never been seen before



1 Minute
and you're done!

Different spot size Handle color optional



12*20mm



12*35mm



12*20mm



12*35mm

808nm 808nm

1) 10 .808nm 808nm 10-40 ,808nm 16 / 808nm 12 / 808nm

.808nm 808nm 808nm 38 * 12 / 808nm 20 * 12 808nm 808nm (2

.808nm 808nm 808nm 808nm 808nm ,808nm 808nm 808nm 808nm (3

808nm 808nm 808nm 808nm ,808nm 808nm 808nm 808nm (4.

808 Hair Removal treatment pictures




808nm 808nm

755 808nm 808nm 3 808nm 808nm 808nm 1064nm, 808nm 808nm 808nm 808nm .


	755 nm for white skin (fine, golden hair removal);
	808nm for yellow neutral skin (brown hair removal);
	1064nm for black skin (black hair removal)



A natural



B energy absorbed by hair




C hair follicle died


Treatment effect



Hair in the treatment area can be easily pulled out



Before




After



Before



After



Before



After

Before



After



□□□□□ □□□□□□

1. □□□□□ □□□□□ , ' □□□□ 14 □□□□□ □□□□ □□□ □□□
- .□□□□□□□ □□□ □□□□ 6 ,□□□ □□□□ ,□□□□ / □□□ .2
- .□□□ □□□ □□□ □□□□□□ .3
- □□□□□ .4 OEM □□□□□ / □□□□□) □□□□□...)



Packing

safe and thoughtful packaging service



Built-in prevention Collision bubble

Two-year warranty for machine handle as consumable,
one-year warranty.

OEM&ODM service for distributor.

Tight packaging

Training: (Video+Manual+Online Service)
Can Keep You Operate It Easily.



3-5 business days delivery

Professional guide:
24 Hours Professional online customer service,



1. 明良科技 mingliangkj:

明良科技 是一家专业从事 包装 设备 研发、生产、销售 13 年。

Company advantage

Service users all over the world



2. OEM / ODM

>> OEM .
OEM .

<< OEM .

<< OEM.

>> OEM .

Custom Section

CASE design



LOGO design



SYSTEM design




3. 000000 00000 000000 0"00 0000

RESEARCH AND DEVELOPMENT

Weifang Mingliangkj electronics Co., Ltd

We have professional Production R & D department, From design research and development to production, every step is strictly checked to ensure product quality.



4. 荣誉资质

