



Picosecond laser

picosencond

>> Instantaneous blasting ;

>> Instantaneous blasting , , ,

>> Imported stone Q-switch , Q-switch.

>> ,



HANDLE-ADVANTAGE



specification

- **Multiple choice**
fixed 1064nm & 532nm, adjustable 1064nm & 532nm (adjust 1-7 mm) for tattoo removal, nevus removal etc.
- **Multifunction**
1320nm for skin rejuvenation
- **Indicator light**
Dot position is the indicator light position dot more accurate



Adjustable
532nm



Adjustable
1064nm



Black doll
1320nm



Fixed
755nm



Fixed
532nm



Fixed
1064nm



.0" 7 00 0" 1-0 000000 0000 00 0000000 000000 00000

1064 nm/532nm, 1064 nm/532nm/1320nm/755nm.

Working Principle



* 1064/532 nm 照射, 照射 1 回, 照射時間 10 分, 照射場所 顔面 Nevus of Ota, 照射後 1 週間経過観察.

* 1320nm 光源 照射 , 照射時間 10 分 , 照射 距離 10cm 程度 .

* 755nm 測定 結果 , 測定 結果 測定 結果 測定 結果

□□□ □□□□□□, □□□□□□, □□□

* 1-7 1064/532



Professional Screen, Easy operation



8.4 该设备采用先进的激光技术，能够实现多种皮肤问题的治疗，如纹身去除、色素痣去除、面部纹身去除、唇线去除、唇线去除、面部纹身去除等。该设备操作简单，易于使用，是您美容院的理想选择。

联系我们

APPLICATION	1)Tattoo removal 2)Eyebrow embroidery removal 3)Eyeline removal 4)Freckles removal 5)Skin rejuvenation 6)Lipline removal 7)Pigment treatment 8)Whitening
wavelength	1064nm&532nm&755 nm &1320nm &1064nm(Adjustable)&532nm(Adjustable)
Pulse energy	1-1500MJ/CM
Width of Pulse	0-10ns
Frequency	1-10HZ
Light spot	1-7mm
Power supply:	220V, 6A or 110V, 12A
color	Blue and black color
Packing method	Aluminum Packing
N.W	20kg
G.W	30kg
Machine	35cm*45cm*35cm(L*W*H)
Aluminum box	46*49*60cm(L*W*H)



Plastic foam:6cm



strong and beautiful
aluminum alloy case



N.W 20KG



G.W 30KG



15 Years Laser Beauty Decvice Manuafactor

- High Feedback
Top10 Supplier

- OEM & ODM
SERVICE

Premium OEM Factories

High-performance manufacturing capacity
R&D capability for customization
Professional certifications and approvals

Our factory is located in the heart of the manufacturing hub, with a large area of 10,000 square meters. We have a complete production line and a professional R&D team. We can provide OEM and ODM services for our customers. We have a good reputation in the market and a large number of customers. We are committed to providing high-quality products and services to our customers.



Custom Services

Customized service to meet your needs




CUSTOM SCREEN



MACHINE COLORS



MACHINE SYSTEM



TROLLEY ALUMINUM BOX



PHONE HOLDER