





0000 000000



00000	808V19
00000 000	808 00000 00000nm 755/808/1064 00nm 3 000000 0000
000000000	4 '0000 14 000K 0000 00000
000 00000	755/808/1064
00000	20-40 00000 000000
00000000000	10~150 j/cm2, 00000000
000000	1-10HZ
00000000000	00000000000000
000000	3500W
00000 0000	12*24 000000 0" 36*12 00 0"
000	110V/60HZ 220 00V/50HZ 000000
000 0000	95 0"

105 英寸
 53*40*105 英寸
 125*56*70.4
 英寸

Handle display

① Optional 12*24mm/12*36mm light spot size.

Different spot size meet different body parts hair removal needs .



② 10bars 1200w / 15bars 1800w. 10million—40million shots.
Effective for permanent hair removal

③ 755nm and 808nm and 1064nm , suits for all skin and hair types.

Cooling effect

The handle has a cooling effect that improve treatment comfort.



4cm²



Three Simultaneous Wavelengths in One Applicator

Plus Exceptionally 4cm² Large Sport
Size



The lowest handle
temperature can reach -27°C



For all skin types

Triple wavelength laser work together

755
nm

808
nm

1064
nm

755nm/808nm/1064nm

755nm
808nm
1064nm

755 755nm 808nm 1064nm, 755nm 808nm 1064nm, 755nm 808nm 1064nm, 755nm 808nm 1064nm.


755nm .(755nm/808nm) 755nm 808nm 1064nm

808nm .(808nm) 755nm 808nm 1064nm

1064nm .(1064nm) 755nm 808nm 1064nm

755nm 808nm 1064nm 755nm 808nm 1064nm 755nm 808nm 1064nm

working principle



755 nm for white skin (fine, golden hair removal);



808nm for yellow neutral skin (brown hair removal);




1064nm for black skin (black hair removal)



A natural




B energy absorbed by hair



C hair follicle died

working principle

Triple wavelength laser spots work together




□□□□ □□□□ □□□□ □□□□□□

Scope of application

Suitable for any unwanted hair on areas like face, arms, armpits, chest, back, bikini, legs...









We help you

Goodbye to the embarrassment



Before



After



Before



After



Before



After

000 00000 00000

System Function



- 4k high definition screen system
- Different parts can be selected
- 6 skin type Any language could be added
- Logo could be added for free
- Easy to operate
- Stable operation

The screen of Alma soprano titanium

- 14 inch big screen, quick touch, easy operate
- Male & female, 6 body parts, 6 skin types
- 6 language options, your native language can be added

Our certificate

All the process of the producing is under ISO 13485 Quality system and match with CE certification request.



BV-France's most authoritative
certification body BV Group certification



TUV-Germany's most authoritative
certification body Rheinland certification



SGS-Switzerland's most authoritative
certification body SGS certification

