



DIODE LASER HAIR REMOVAL MACHINE

- SUPER ICE PAINLESS EXPERIENCE
- PERMANENT HAIR REMOVAL
- COMFORTABLE HAIR REMOVAL

1min} Fast and painless hair removal
One minute cooling -21°C

□□□□□□□□ □□□□□□

1.3 755 □□□□□□ 808 □□□□□□ □□□□□□ 1064 □□□□nm, □□□□ □□□□ □□□ 1-□ 3-□ □□□□□□ □□□□


1000 □□ □□□□ □□□□ :□□□□ □□□□W/1200W/1600W □□□□□□□□□□

!□□□□ □□□□ □□□□ □□□□□□□□"□ 35*12 ,□"□ 25*15 □□□□□□ □□□□□□ .2

□□□□□□ □□□□□□ :□□□□□□ □□□□□□ .3 Dual-TEC ,□□□□ □□ □□□□□□ □□ □□□□□□ □□□ □□□□□□ □□□□□□□□ ,□□□□□□□□□□ .□□□□ 24 □□□□□□ □□□ □□□

□□□□□□ □□□□ □□□□□□ □□□□□□ :□□□□□□□□□□ .4


3 in 1 all skin type can be used



755 nm for white skin (fine, golden hair removal);



808 nm for yellow neutral skin (brown hair removal);



1064 nm for black skin (black hair removal)

□□□ □□□□□□ □□□□□ □□□□□□ □□□□ □□□□□ □□□□□.

- □□□ □□ □□□ □□□ □□□□□ □□□□□□□□□□ □□□;
- □□□ □□ □□□ □□□ □□□□□;
- □□□□□ □□□□□.
- □□□□ □□□□□□□□ □□□□□□□□ □□□□ □□□□;
- □□□□□□□□□□ □□□□□□ □□ □□□□;

TEC cooling system

One minute cooling -21°C

Best **TEC Cooling** system
hair remover laser



TEC cooling system : Dual-TEC , TEC cooling system TEC cooling system TEC cooling system , TEC cooling system
TEC cooling system 24 TEC cooling system TEC cooling system.

Available in **black or white**



working principle

Make Your Beauty Business More Easier



Hair removal also stimulates collagen regeneration, shrinks pores and makes skin firm and smooth



755nm 808nm 1064nm ,755nm 808nm :755nm 808nm 1064nm 755nm 808nm 1064nm .



755nm 808nm 1064nm ,755nm 1064nm 808nm 755nm 808nm 1064nm .


755nm (755nm/1064nm) 755nm 808nm 1064nm .

808nm (808nm) 808nm 1064nm 755nm .

1064nm (1064nm) 1064nm 808nm 755nm .

755nm 808nm 1064nm 755nm 808nm 1064nm .

Treatment effect comparison



雷射脫毛 脫毛 脫毛 : 脫毛

雷射脫毛 脫毛 脫毛 脫毛 脫毛 脫毛 ICE 脫毛 脫毛 脫毛 脫毛 脫毛 脫毛

雷射脫毛 脫毛 脫毛	755/808/1064 雷射脫毛 脫毛 脫毛 脫毛 脫毛 脫毛 脫毛 脫毛
------------	--

總功率	3000W;
電磁輻射 電磁場 電磁波	0-150J/cm2 (電磁場 電磁波)
響應時間 響應 響應	10-800ms (電磁場 電磁波);
電壓 電壓 電壓	1-10 V;
電壓 電壓	25*15 mm ² /10*20mm ²
電壓 LCD 電壓	電壓 LCD 10.4TFT True Color
電壓 電壓 電壓 電:	電壓 電壓 TEC 電 電壓 12 電 10 電 電壓
電壓 電壓	105*40*40 mm
電壓 電壓:	115*59*61 mm
電壓 電壓	35 mm
電壓 電壓	220V/50HZ 110 V/60HZ

電壓 電 電壓

電 電壓 電壓 電壓 電壓 電壓 電壓 電

About the Shipping

**We can offer the door to door services
by air or by sea** just depend on your actual request.

Such as DHL,UPS,TNT,FEDEX...



Packing

safe and thoughtful packaging service



Built-in prevention Collision bubble

Two-year warranty for machine handle as consumable,
one-year warranty.

OEM&ODM service for distributor.

Tight packaging

Training: (Video+Manual+Online Service)
Can Keep You Operate It Easily.



3-5 business days delivery

Professional guide:
24 Hours Professional online customer service,

□□□□□ □□□:	3 □□□□□ □□□.
□□□□□ □□□□:	□□□□ ,□□□□ □□□□ □□□□□ □□□□□ DHL, UPS, FedEx, TNT □□□'.
□□□□□□□□□:	□□□ □□ □□□□□□□□□□ □□□□□