

All-in-One Aesthetic System



000000 000000 ,0000000 808 000000 000000 00000 00000 00000 - 00000 000000 000000 00000 000000 00000000 000000
 00000000 00000 0000 00 0000 .0000000000 0000 0000000000 00 00000000 - 00000 000000 000000 00000 000000 000000 00 00000
 00000000 0000 ,0000000 000000 0000 00 ,000000 000000 000000 00000 00000 000000 ,00000000 000000 000000 00000 00000
 00000 00000 000000 0000 00000000 0000 .0000000000 000000 000000 00000000 00000000 00000000 000000 00000000
 808 000000 000000 000000 ,808 000000 000000NM, 00 0000000 0000 .3 00 00000 000000 00000 00000 00000000
 00000000 0000000 00000 000000 000000 00000000 000000 000000 000000 ,00000000 000000 00000 00000 00000000 0000000000
 00000000 00000 00000 000000 ,00000000 00000 00000000 000000 00000 000000 00 0000 00000000 00000000 00 000000 .000000
 0000000000 000000 00000 00000 0000000000 0000000000.

Trusted by Laser Experts Across the Word



US AGENT

Cooperation since 2023



UK AGENT

Cooperation since 2015



CANADIAN AGENT

Cooperation since 2020



Netherlands Agent

Cooperation since 2018



GERMAN AGENT

Cooperation since 2010



SWEDISH AGENT

Cooperation since 2009



DENMARK AGENT

Cooperation since 2020



FINLAND AGENT

Cooperation since 2020



AUSTRALIA AGENT

Cooperation since 2008



FRENCH AGENT

Cooperation since 2022

MLKJ 代理雷射儀器 2008 年開始，至今已在 20 多個國家及地區設有代理。

MLKJ 代理雷射儀器 2008 年開始，至今已在 20 多個國家及地區設有代理。

MLKJ 代理雷射儀器 2008 年開始，至今已在 20 多個國家及地區設有代理。



MOOTH SKIN STARTS HERE

Professional results made simple, safe, and effective.

7 KEY ADVANTAGES OF OUR MACHINE

EFFECTIVE
RESULTS

COMFORTABLE
PROCEDURE

LOW MAINTENANCE,
HIGH VALUE

SUITABLE FOR
ALL SKIN TONES
AND AREAS

SMART AND
ADVANCED
TECHNOLOGY

SAFE FOR
THE SKIN

FAST AND
TIME-SAVING





本公司 Mingliang Technology 产品 已 通过 FDA (美国), MDL (加拿大- CE 认证),

并 获得 2025 年 加拿大 美容 专业人士 选择 奖。



MAXIMIZE YOUR ROI

Reliable technology. Proven results.
Zero hidden fees.



* 100% 100%

* 100% 100%

* 100% 100% - 100% 100%

* 100% 100%

* 100% 100% - ROI 100%

100% 100% 100% .100% 100% .100% 100%.

Precision angle control for customized treatment positions

Precision angle control for customized treatment positions

1111

□□□□□ □□□□□ □□□□ □□□□ □□□□ □□□□ □□□□ □□□□

All-in-one handle with high-resolution screen

All-in-one handle with high-resolution screen

[illegible]



LASER HAIR REMOVAL

- 808nm Wavelength – Targets deep follicles for precise hair removal
- Fast & Painless – Large spot size, smooth-glide treatment
- Safe for All Skin Types – Fitzpatrick I-VI compatible
- Sapphire Contact Cooling – Protects skin, enhances comfort
- Long-Lasting Results – Slows regrowth, fewer sessions needed

• 808nm Wavelength - Targets deep follicles for precise hair removal
 Fast & Painless, Large spot size, smooth-glide treatment
 Safe for All Skin Types - Fitzpatrick I-VI compatible
 Sapphire Contact Cooling - Protects skin, enhances comfort
 Long-Lasting Results - Slows regrowth, fewer sessions needed

@Long-Lasting Results

Diode Laser Hair Removal – Key Benefits



Safe for All Skin Types



Screen interaction



Fast & Painless



Three Wavelength



Silent




Ergonomics




Laser hair removal


- Selective Photothermolysis – Permanent Hair Reduction
- Safe for all skin types with minimal side effects
- Precise treatment zones – no damage to surrounding skin
- Up to two times longer-lasting results compared to standard treatments
- Faster sessions with advanced cooling for comfort
- Fast Coverage for Large and Small Areas
- Clinically proven technology used in top medical clinics



Adjustable cooling Comfortable but not exciting



EXFU LASER Thermal image map



Thermal image of ordinary depilator

Instantaneous temperature: -31°C



Ordinary machine: 10-20°C




Data source: EXFU Technology Research and Development Laboratory

Test conditions: Boot test at room temperature -22°C under normal conditions of third class skin cooling

Whole body hair removal, Ice feel painless

Releasing the laser generates heat, and better cooling techniques are needed to balance the heat
Achieve a comfortable temperature for painless hair removal.



Safety • Simple • Enjoy

All-in-One Care One Smart Device



Enjoy Multi-Function Treatment— At No Extra Cost!



我们提供 OEM 和 ODM 服务 - 我们拥有专业的研发团队，可以根据客户的需求进行定制开发。



我们拥有专业的研发团队，可以根据客户的需求进行定制开发。我们提供 OEM 和 ODM 服务 - 我们拥有专业的研发团队，可以根据客户的需求进行定制开发。

Product Parameter								
Device Name	Diode laser hair removal machine							
Model Number	Vertical EXFU 808 V2							
Wavelength	□ 808mmtechnology □ 755+808+1064mm □ 755+808+940+1064nm							
Screen size	14 inch 4K Style touch screen							
Pulse Duration	1-300ms							
Frequency	1-10hz							
Spot size	□	12*20mm	□	12*35mm	□	12*24mm	□	12*36
Energy	1-150J/cm2							
Cooling System	□	Air cooling+TEC cooling +Water cooling +Sapphire Substrate	□	Compressor Cooling +Water Cooling +Sapphire Substrate+Air cooling				
Voltage	□	AC220V 50HZ	□	AC110V 60HZ				
Dimension of machine	429*422*1265mm							
Package	Aluminum box							
Warranty	2 years for machine , 1 year for handle							

1. 本機為垂直式設計，操作簡便，省時省力。
 2. 本機採用最先進的半導體雷射技術，能量穩定，安全無痛。
 3. 本機配備多種波長，可適用於不同膚質及毛髮。
 4. 本機具有多種脈寬及頻率選擇，可滿足不同客戶需求。
 5. 本機配備多種光斑尺寸，可適用於不同部位。
 6. 本機具有多種能量選擇，可滿足不同客戶需求。
 7. 本機具有多種脈寬及頻率選擇，可滿足不同客戶需求。
 8. 本機具有多種光斑尺寸，可適用於不同部位。
 9. 本機具有多種能量選擇，可滿足不同客戶需求。
 10. 本機具有多種脈寬及頻率選擇，可滿足不同客戶需求。

產品名稱	垂直式雷射脫毛機															
型號	EXFU 808 垂直式 V2															
雷射波長	□ 808 7558089401064 □ 755 7558081064 □ 7558089401064nm															
螢幕尺寸	14 吋 4K 觸控螢幕															
脈寬	1-300ms															
頻率	1-10 Hz															
光斑尺寸	□	12*20 mm			□	12*35 mm			□	12*24 mm			□	12*36		
能量	1-150J/cm2															
冷卻系統	□	Air cooling+TEC cooling +Water cooling +Sapphire Substrate				□	Compressor Cooling +Water Cooling +Sapphire Substrate+Air cooling									
電壓	□	AC220V 50HZZ				□	AC110V 60Hz									
機身尺寸	429*422*1265 mm															
包裝	鋁合金箱															
保固	機器保固 2 年 ,手柄保固 1 年															

1. 本機為垂直式設計，操作簡便，省時省力。
 2. 本機採用最先進的半導體雷射技術，能量穩定，安全無痛。
 3. 本機配備多種波長，可適用於不同膚質及毛髮。
 4. 本機具有多種脈寬及頻率選擇，可滿足不同客戶需求。
 5. 本機配備多種光斑尺寸，可適用於不同部位。
 6. 本機具有多種能量選擇，可滿足不同客戶需求。
 7. 本機具有多種脈寬及頻率選擇，可滿足不同客戶需求。
 8. 本機具有多種光斑尺寸，可適用於不同部位。
 9. 本機具有多種能量選擇，可滿足不同客戶需求。
 10. 本機具有多種脈寬及頻率選擇，可滿足不同客戶需求。



High Feedback Top10 Supplier
OEM & ODM Professional Design



Authentication

FDA,NQA13485,CB certification
and more Complete certification
materials



60000+ Customers

We have professional after sale
team and we provide 7*24
services



2 Years Warranty

2 years warranty for each
machine, All questions will get
reponse within 24 hours



包装方式:	7 包装方式.
包装材料:	纸箱, 泡沫, 气泡膜, 木箱, 托盘, DHL, UPS, FedEx, TNT 等.
包装要求:	包装 需 符合 国际 标准