





PAINLESS FOREVER DIODE LASER HAIR REMOVAL

- 100% 100% 100% TEC 100% 100% 100% , 100% 100% 100% 100% , 100% 100% .
- 100% 100% 100% 100% , °C 5-3- 100% 100% 100% 100% , 100% 100% 100% 100% 100% .
- 100% 100% 100% , 100% 100% 1 , 100% 2 , 100% 100% 100% .
- 100% 100% 100% 100% 100% 100% 100% .



1600 1000 1000 1000 1000 1000W 1000 1000.

For all skin types



755nm / 808nm / 1064 nm

1000 1000:

- 1000 16 1000 1000 1000 1000W, 1000 35*12 1000 1000
- 1000 1000 1000 1000 1000 1000 1000 1000 1000 1000.
- 1000 1000 1000 1000 1000 1000.



- 1600 ןװאט ןװאטערע ןװאט ןװאט ןװאטW ןװאט 14 ןװאט ןװאטערע ןװאט ןװאט ןװאטערע'.
- ןװאטערע ןװאט ,ןןן ןװאט ןװאט ןװאט ןװאט.

ןןןןן ןװאטערע ןװאטערע ןװאטערע ןװאט ןװאט.

Power cord classification



ןןןןן ןװאט

ןןןןן ןװאט	ןןןןן ןװאטערע ןװאטערע ןװאט ןװאט ןװאטערע ןװאט
ןןןןן ןװאט	ןןןןן ןװאט
ןןןןן ןװאט	3-5 ןװאט ןװאט ןװאט ןװאט
ןןןןן ןװאט	ןןןן ןװאטערע ןװאט ןװאט ןװאט ןװאט DHL
ןןןןן ןװאט ןװאט	ןןןן ןװאט ןװאט ןװאט ןװאט ,ןן ןװאט ןװאט ןװאט

PACKAGING



Built-in prevention
Collision bubble



Tight packaging



3-5 business days
delivery