

Medical handle is Lighter handle

Stronger, Faster, Smarter

1600w big handle power 24 hours working Painless hair removal



● 12*24mm²



● 12*36mm²

[Learn more](#)



MLKJ 13

13 60,000 , 102 , ,

MLKJ——

Machine advantage:

- Machine warranty 2 years
- Custom language system
- 1800w high power hair removal
- Fast and safe



1064nm

1064nm 1.3nm 808nm 755nm, 1-3 1-3

1200W /1800W

! 36*12, 24*12

3 Dual-TEC

24


4

TEC cooling system

One minute cooling -21°C

Best **TEC Cooling** system
hair remover laser





00000000 000000 00000000 00000 00000 00 00000000:

»».000000 000000 0000 ,00000 0000 ,000000 0000000000 00000 000000 0000 ,00000 000000 0000 :00000000
 00000 000000 00000 00 000000 00000 000000 ,0" 36*12 000000 000000 00000 :000000««
 .00000 0000 00000 ,00000 00000 00 00 000000 00 00 0000 :0000000000 00000 00000««
 00000000 0000000 00000000 00 0000000000 00000 00 00000000 ,°C5-3~ :00000 0000000000 ««.
 00000 00000

Hair removal principle

Make Your Beauty Business More Easier





The laser selectively acts on the melanin in the hair follicle, destroying the hair-growing area

Natural hair loss, prevent regeneration, and achieve the purpose of hair removal

Hair removal also stimulates collagen regeneration, shrinks pores and makes skin firm and smooth





	755 nm for white skin (fine, golden hair removal);
	808 nm for yellow neutral skin (brown hair removal);
	1064 nm for black skin (black hair removal)

□□□□ □□□□ **20-40** □□□□ □□□□ □□ □□□□

0000 000 00 00 00000 000000 0000 000000 000000
000000000 000000 000000 0000 0000 00 000 0000

□□□□ □□ 808 □□□□ □□□□nm □□□□ 3 755/808/1064 □□

□□□□□□□□ □□□□ 14 □□□□□□ □□□ □□□ □□□□□□'

□□ □□□□ 808 □□□□□ 755/808/1064 □□ □□□□□

□□□□□ 40 □□□□□ □□□□□□

照射量 10~150 j/cm², 照射回数

□□□□□ 1-10HZ

TEC

□□□□□□ 3000W

□□□□ □□□□ 12*36 □□□□□ □"□ 24*12 □□ □"□

110V/60HZ 220 V/50HZ

1)

□□□□ 6 □□ □□□ (2


በሰነድ ይጻፉ ለሰነድ ማረጋገጫ ማስቀመጥ ይቻላል፡፡ (3! ማስቀመጥ)

Certificate display

Certificate is the best guarantee for you




safe and thoughtful packaging service



OEM&ODM service for distributor.

Training: (Video+Manual+Online Service)
Can Keep You Operate It Easily.



□ □ □ □ □ □ □ □ □ □ □ □

1. 姓名 Weifang Mingliang 性别 男 出生日期 1993 年 12 月

Customer visit



2. 醫藥器械 醫藥器械 醫藥器械 醫藥器械 醫藥器械 醫藥器械
3. 醫藥器械 醫藥器械 醫藥器械 ,醫藥器械 醫藥器械 OEM, 醫藥器械 醫藥器械 OEM, 醫藥器械 醫藥器械 醫藥器械....

Research and Development

We have professional Production R & D department.
From design research and development to production, every step is strictly checked to ensure product quality.



CAD and PCB drawing



Electrical schematic diagram and preparation procedures



Ammeter test



Install the motherboard



Assemble the hardware



Leave the factory after passing the inspection

