

我们 OEM / ODM
我们 产品 我们 , 我们 我们

Build more trusted partners

Our customers

60000+ CUSTOMERS

OEM/ODM

Customize the machine according to customer needs



CERTIFICATE

Obtained multi-way authoritative certification,
product testing certification, product patent authority,



我们 我们
我们 我们 我们 我们 我们 我们
我们-我们 我们 我们 我们 我们 我们 我们 我们



Stronger, Faster Two Handles

With 14-inch HD 4K Screen

□□□□□□

*.□□□□ □□□□□□ □□ □"□□□ □□□□□ □□□□□ □□

.□□□□ □□□□ □□□□□ □□□□ □□ □□□□ 3-□ □□□□ ,□□□□□ □□□□□□ 40-□ □□□□ *

808 *nm □□□□ □□□□ □□□ □□□□□□ □□□□

1200 □□ □□□□ □□□□ :□□□□□ □□□□ *W /1800W □□□□□□□□□

!□□□□ □□□□ □□□□ □□□□□ □□□□□ ,□"□ 36*12 □□ □"□ 24*12 □□□□□ □□□□□ □□□□□ □□□□□ *

□□□□□ □□□□□ :□□□□□ □□□□□ * Dual-TEC □□□□□□ □□ □□□□□ □□□□□□ □□□ □□□□□ □□□□□□ ,□□□□□□□□

.□□□□□□ □□□ □□□ □□□□ 24 ,□□□□□ □□

□□□□□□ □□□□□□ 40 :□□□□□□□ □□□□□ *



DIODE LASER

1200W / 1800W Soprano Titanium hair removal machine

1. □□□□ □□□□□

12*24mm or 12*36mm handle

Suitable for any unwanted hair on areas like face, arms, armpits, chest, back, bikini, legs...



2.1200w, 1800w 36*12 24*12 3000 3000 .300000 300000 3000 3000.

*350 300000 300000 300000 ,30000 3000 ,300000 30000 3000
30000 30000 ,(3000000 3000000 3000) 3000000 3000 3000 3000000 3000 ,3000000 3000000 3000 *



3.300000

* 3000 30000 30000 ,3000 3000000 ,30000000 3000 300000

* □□□□ □□ □□□□ □□□□ □□□□ □□□□ □□□□ □□□□ □□□□

* □□□□ □□□□□ □□□ □□□□□ □□□□ □□□□ □□□□

Handle display

① Optional 12*24mm/12*36mm light spot size.

Different spot size meet different body parts hair removal needs .



2 10bars 1200w / 15bars 1800w. 10million—40million shots.
Effective for permanent hair removal

3 755nm and 808nm and 1064nm , suits for all skin and hair types.

Cooling effect

The handle has a cooling effect that improve treatment comfort.



--	--	--	--	--	--	--	--

Hair removal comparison

The real picture taken by the customer

Different parts of men and women, as well as different skin colors can have very good hair removal results, they all get a permanent and painless hair removal experience



Before



After Treatment

Hair removal comparison

The real picture taken by the customer

Different parts of men and women, as well as different skin colors can have very good hair removal results, they all get a permanent and painless hair removal experience



Before



After Treatment

4. 1. 2. 3. 4. OEM (1000/1000) (1000...)

New upgrade system

The newscreen is clear easy to operate.



5. 000000 OEM/ODM

- >>OEM your own machine body
- >>OEM your own program software
- >>OEM pretty machine colors
- >>Print your LOGO on machine body and screen
- >>R & D team and Quality inspection Show

[illegible]