


Working Principle

Suits for all skin and hair types



- **755nm for white skin** (fine, golden hair removal)
- **808nm for yellow neutral skin** (brown hair removal)
- **1064nm for black skin** (black hair removal)

* 0.5cm 35*12 , 0.5cm 20*12 0.5cm 0.5cm
0.5cm 0.5cm 0.5cm 0.5cm , 0.5cm 0.5cm , 0.5cm 450 0.5cm*
0.5cm 0.5cm , (0.5cm 0.5cm 0.5cm) 0.5cm 0.5cm 0.5cm 0.5cm , 0.5cm 0.5cm 0.5cm *



□□□□ □□

□□□□ □□□□□ □□□□□□ □□□□ □□□□□ □□□□□

□□□□□ □□

□□□□ 16 ,□□□□ 12 ,□□□□ 10 ,□□□□ □"□□□□/□□□□□□□□

□□□ □□□□□

755 □□□□□□ 1064 □□□□□□ 808 □□□□□□

□□□□□□□□□□□□

0-150J/cm2

□□□□□□□

1-10hz

□□□□ □□□□

40-800ms

□□□□ LCD □□□□□□□□ □□□□ 12 □□□ □□□' True Color

□□□□□ □□□□□

□□□□□ □□□□□□□□ □□□□□ □□□□□□□□ □□ □□□□ □□□□ □□□□□ □□□□□ □□□□ □□□□ □□□□□□□□

□□□□□□□

4000W


□□□□□ □□□□□

220V/50HZ 110 □□V/60HZ

RESEARCH AND DEVELOPMENT

Weifang Mingliangkj electronics Co., Ltd

We have professional Production R & D department, From design research and development to production, every step is strictly checked to ensure product quality.



CERTIFICATE DISPLAY



Packing

safe and thoughtful packaging service



Built-in prevention Collision bubble

Two-year warranty for machine handle as consumable,
one-year warranty.

OEM&ODM service for distributor.

Tight packaging

Training: (Video+Manual+Online Service)
Can Keep You Operate It Easily.



3-5 business days delivery

Professional guide:
24 Hours Professional online customer service,

