



1.3 1064 nm 808 nm 755nm, 1-3 1000 :W/1200W/1600W ! 35*12 , 20*12 . 2. Dual-TEC 3. 24 , 4. :





Different spot size Handle color optional



□□□□ □□□□ □□□ □□□□ □□□□□

Alex 755nm □□□□ □□□□

808 □□□□□□ □□□□□nm □□□□ □□□□

Long Pulse 1064nm □□□□ □□□ □□□□

Treatment effect



□□□□□

1. □□□ □□□□ 6 □□□□□□ □□□□ □□□□□ ,□□□ □□□□ 6 ,□□□□□ □□□□□
- □□□ □□□ □□ □□□□□□ □□□□□ ,□□□ □□□□□□□□□□ 6 .2
- □□□□□ .3 OEM □□□□□□/□□□□□) □□□□□□...

