

□□□□ □□□□ 40 :□□□□□□ □□□□ *

Four handheld barcode scanners are shown in a row. The first two are black with a gold-colored scanning head, and the last two are white with a gold-colored scanning head. They are all standing upright on a reflective surface.

□□□□ □□□□ ,(□□□□□ □□□□□ □□) □□□□□ □□□ □□ □□□□□□ □□□ ,□□□□□ □□□□□ □□ *



1. 優點 優點 優點

- * 優點 優點 優點 ,優點 優點 ,優點優點 優點 優點
- * 優點 優點 優點 優點 優點 優點 優點 優點
- * 優點 優點優點 優點 優點優點 優點 優點 優點

12*24mm or 12*36mm handle

Suitable for any unwanted hair on areas like face, arms, armpits, chest, back, bikini, legs...




2. 優點 優點 優點 優點優點 優點

1. Alex 755nm 優點 優點

2. 808nm 808nm 808nm 808nm

3. Long Pulse 1064nm 1064nm 1064nm 1064nm



3. 808nm 808nm

Hair removal comparison

The real picture taken by the customer

Different parts of men and women, as well as different skin colors can have very good hair removal results, they all get a permanent and painless hair removal experience



Before



After Treatment

Hair removal comparison

The real picture taken by the customer

Different parts of men and women, as well as different skin colors can have very good hair removal results, they all get a permanent and painless hair removal experience



Before



After Treatment

4. 14 days before treatment

14 days before treatment, 14 days before treatment

14 days before treatment, 14 days before treatment, 14 days before treatment

14 days before treatment, 14 days before treatment, 14 days before treatment

14 days before treatment, 14 days before treatment, 14 days before treatment

5. OEM/ODM

>>OEM your own machine body

>>OEM your own program software

>>OEM pretty machine colors

>>Print your LOGO on machine body and screen


>>R & D team and Quality inspection Show

6. 14 days before treatment

000000 00000 000000 00 .00000000 000000 00 .00000000 0"00000 00000000 000000 000000 0"00 000000
00 00000000 00000000 00 000000 00000000 00000000 0000 0000 0000 0000 00 .000000 000000 000000 000000
00000000 000000.

SHIPPING

Welcome to visit our factory



In terms of following trade details:

- 1)The shipping cost are based on DHL cost to your country
- 2)Delivery time:3-5 days after receiving payments.
- 3)Payment terms:T/T(bank transfer),Western Union.
- 4)Warranty:2 years for the whole machine
- 5)Warranty Policy:one month guarantee replacement (we bear all shipping cost),2years warranty,lifelong maintenance.
- 6)Packing method: Aluminum box with hard plastic foam.
- 7)Free-training to customers:Free We could offer DVD and User's manual and 10 Hours online service to our customers
- 8)Certifications:CE TUV ISO 13485
- 9)MOQ:1 UNIT
- 10)The quotation here above is valid within 1 month