




1. 10000 10000 10000000 1000000.
 2. 10000 100000 10000 100000 40,000,000 ,10000000 10"10000 100 100000000 100000000 1000000 1000000.
 3. 10000 ,1000000 1000 ,10000 ,10000
 4. 1000000 1000 1000 10000 1000000
- 1000 10000 6 100 '10000 5.14.0 1000000 1000000 10000000 1000 1000.



- 100000 1000000 20-40 10000 10000 ,10"10000 100000 100000 100
- 3 ,100000 10000000000D 7558081064nm 808 10000000 1000000 100nm

---- 1000 , 1200w 1600-1800w 100 1000w

---- 38*12 , 25*15 , 20*12 1000w 1000w 1000w

---- 1000w 1000w 1000w 1000w 1000w 1000w 1000w 450 1000w 1000w 1000w

---- 1000w 1000w 1000w , 1000w 1000w 1000w



MACHINE DETAILS DISPLAY

EXQUISITE DETAIL DISPLAY



□□□□ □□□□

Three Simultaneous Wavelengths in one Applicator

12mm*20mm / 12mm*35

Mix Laser 755nm+808nm+1064nm
Multiple Laser Wavelengths and Technologies

Alex 755nm
Ideal for range of hair colors

Speed 808nm
Safe for darker skin types




YAG 1064nm
Perfect solution for darker skin

□□□□ □□□□ □□□ □□□□□□□□ □□□□□□

1.Alex 755nm □□□□ □□□□

2. 808 □□□□□□□ □□□□□nm □□□□ □□□□

3.Long Pulse 1064nm □□□□ □□□ □□□□



- **755nm for white skin** (fine, golden hair removal)
- **808nm for yellow neutral skin** (brown hair removal)
- **1064nm for black skin** (black hair removal)

□□□□ □□□□□□



□□□□□ □□□
 □□□□□□ □□□□□□□□
 □□□□□ □□
 □□□□□□□□□□□□□□
 □□□ □□□
 □□□□□ □□□
 □□□□□ □□□□□
 □□□ □□□□□

10-300ms □□□□□□□□
 -27°C~5°C
 10bar/12bar/16bar, □"□□□□/□□□□□□□□ □□□□□
 7558081064 □□□□ □□□nm □□□□□□□□□□
 1000w/1200w/1600w
 808 □□□□□ □□□□□nm 755/808/1064 □□nm 3 □□□□□□□ □□□□
 □□□□ 12 □□□'
 755/808/1064

適用年齡	20-40 歲
適用部位	10~150 j/cm2, 全身
適用頻率	1-10HZ
適用功率	3500W
適用尺寸	12*20 吋
適用電壓	110V/60HZ 220 V/50HZ

其他特點



其他特點

1. 12 吋觸控螢幕，操作簡便

2. 6 吋顯示器，顯示清晰，6 吋顯示器，顯示清晰

3. 6 吋顯示器，顯示清晰，6 吋顯示器，顯示清晰

4. OEM 代工（/）...

其他特點

