



DIODE LASER HAIR REMOVAL MACHINE

*New 3D 755nm 810nm 1064nm technology
Super Ice painless experience
Fast and permanent hair removal*

Zalety maszyny do usuwania włosów laserem diodowym 755 808 1064

- 1) Użyj skraplacza TEC, ma on lepszy efekt chłodzenia, upewnij się, że maszyna pracuje nieprzerwanie przez 24 godziny, nawet latem.
- 2) Użyj importowanej przez Włochy pompy wysokiego ciśnienia, o 40 000 000 dłuższej żywotności
- 3) 2 filtry, 1 filtr do wody miękkiej, 1 filtr do zanieczyszczeń oddzielnie.
- 4) Wysoka moc 2000 w, silna energia, dobry efekt usuwania włosów.

MULTI-ANGLE MACHINE DISPLAY



New upgrade 14-inch HD 4K screen
12*35mm big spot size
Optional parameters for different skin types



ADVANTAGE

- **PAINLESS:** 755/808/1064nm diode laser for all type skin hair removal
- **FASTER:** Large area spot sliding operation
- **NO TRAUMA:** There is no trauma to skin tissue
- **SAFETY:** To avoid the light of the deputy to reduce the difficulty of operation



Before and After

Treatment comparison



• *Cooling effect* •

The handle is frosted for one minute,
making your treatment more comfortable and painless



Suitable for hair removal on any part of the body,
Such as arms, legs, face, armpits, back, chest, etc.



TECHNICAL PARAMETERS

Device Name	Diode laser hair removal machine
Model Number	V30 single handle 4K
Wavelength	755nm 808nm 1064nm
Screen size	14 inch 4K true color touch screen
Pulse Duration	1-300ms
Frequency	1-10hz
Spot size	12*35mm
Energy	1-150J/cm2
Cooling	Water cooling+Air cooling
Voltage	AC220V/110V 50HZ/60HZ
Demension of machine	45.4cm*52.1cm*101cm
Package	Aluminum box
Warranty	2 years

Aby uzyskać więcej informacji o produkcie, skontaktuj się z nami 24 godziny online!