

MLKJ

CUSTOMER SERVICE

15 YEARS FACTORY, 2 YEARS WARRANTY, 102 COUNTRIES, 60,000+ CUSTOMERS.

MLKJ—MAKE YOUR BEAUTY BUSINESS EASIER



15 years factory



2 years warranty



102 COUNTRIES



2 years warranty




14 inch
Screen Size



3000W
Input power



1-10HZ
Frequency



755nm 808nm 1064nm
Wavelength

>>Machine 14-inch large screen

>>3000W machine Moc to ensure the treatment effect

>>1-10 Hz fast Częstotliwość and 15x25mm Rozmiar plamki ensures faster, smooth and effective treatment

>>808 single wave or 755nm/808nm/1064nm perfect triple Długość falis

>>Easy to operate Data Base system,can do the treatment by man mode and women mode, również inna część ciała. Aby zapewnić bezpieczny parametr dla nowego operatora,
>> Long life time More than 40 millions strzały gold laser diode module, anti high temperature.

350g lightweight **handle**, more ergonomic

Available in **black or white**




Rękojeść waży tylko 350g, co jest wygodne w leczeniu

>>12 pieces or 16 pieces Germany Dilas original laser bars,600/800W/1200W power is capable to meet all

demands of hair removal on the whole body;


>>1-10Hz fast frequency and 15x25mm spot size ensures faster, smooth and effective treatment;

>Super sapphire touch Chłodzenie system ensures painless and comfortable treatment;



Hair removal principle



Make Your Beauty Business More Easier



The laser selectively acts on the melanin in the hair follicle, destroying the hair-growing area

Natural hair loss, prevent regeneration, and achieve the purpose of hair removal

Hair removal also stimulates collagen regeneration, shrinks pores and makes skin firm and smooth



755 nm for white skin (fine, golden hair removal);



808 nm for yellow neutral skin (brown hair removal);



1064 nm for black skin (black hair removal)

Uchwyt Długa żywotność 20-40 milionów zdjęć

Prędkość 808nm: Złota standardowa długość fali dla wszystkich rodzajów włosów

Alex 755nm: Specyficzny dla blond włosów, cienkich włosów

Długi impuls 1064nm: specyficzny dla ciemnej, opalonej skóry najlepsza jakość lasera ipl shr opt / nd yag / alexandrite laserowa maszyna do depilacji cena








Model	808V27- laser diodowy
Typ lasera	Laser diodowy 808nm lub 3 fale 755/808/1064
Wyświetlacz	14-calowy ekran dotykowy
Wavelength	808nm/7558081064
shots	20-40 milionów strzałów
Energia	10~150 j/cm2, regulowany
Frequency	1-10HZ
Cooling	Podwójne chłodzenie TEC
Power	3000W
Spot size	12*35mm lub 12*20mm do wyboru
Napięcie	110 V/60 HZ lub 220 V/50 HZ do wyboru

profil firmy

1. Firma Weifang Mingliang ma 15 lat doświadczenia w produkcji urządzeń kosmetycznych w instrumencie kosmetycznym.

Został sprzedany do 102 krajów i obsługuje ponad 600000 instytucji na całym świecie Ułatw biznes kosmetyczny.



2. Obsługuj powłokę maszyny OEM (system maszynowy OEM) może dodać własne logo....

3. Posiadamy profesjonalny dział badawczo-rozwojowy produkcji. Maszyna do pakowania w aluminiowe pudełka jest wytrzymała i trwała, z ochroną bezpieczeństwa, pomagając Twojej maszynie bezpiecznie wrócić do domu!

Packing

safe and thoughtful packaging service



Built-in prevention Collision bubble

Two-year warranty for machine handle as consumable,
one-year warranty.

OEM&ODM service for distributor.

Tight packaging

Training: (Video+Manual+Online Service)
Can Keep You Operate It Easily.



3-5 business days delivery

Professional guide:
24 Hours Professional online customer service,

**Skontaktuj się z nami teraz
24 godziny online!**