



Sync to machine

SMART SCREEN CONTROLLER

Intelligent | Interconnected | Efficient

[Home](#) | [Food](#) | [Drugs](#) | [Medical Devices](#) | [Radiation-Emitting Products](#) | [Vaccines, Blood & Biologics](#) | [Animal & Veterinary](#) | [Cosmetics](#) | [Tobacco Products](#)

[Follow FDA](#) | [En Español](#)

510(k) Premarket Notification

[FDA Home](#) | [Medical Devices](#) | [Databases](#)

[CDRH SuperSearch](#)

[510\(k\)](#) | [DeNovo](#) | [Registration & Listing](#) | [Adverse Events](#) | [Recalls](#) | [PMA](#) | [HDE](#) | [Classification](#) | [Standards](#)
[CFR Title 21](#) | [Radiation-Emitting Products](#) | [X-Ray Assembler](#) | [Medsun Reports](#) | [CLIA](#) | [TPLC](#)

[Back To Search Results](#)

Device Classification Name	Powered Laser Surgical Instrument
510(K) Number	K200525
Device Name	Medical Diode Laser Hair Removal System
Applicant	Weifang Mingliang Electronics CO., LTD No.13426, Yuqing Street, High-Tech District Weifang, CN 261000
Applicant Contact	Li Mingliang
Correspondent	Beijing Believe-Med Technology Service Co., Ltd. Rm. 912, Building#15, XiYueHui, No.5, YiHe North Rd., FangShan District Beijing, CN 102401
Correspondent Contact	Ray Wang
Regulation Number	878.4810
Classification Product Code	GEX
Date Received	03/02/2020
Decision Date	05/27/2020
Decision	Substantially Equivalent (SESE)
Regulation Medical Specialty	General & Plastic Surgery
510k Review Panel	General & Plastic Surgery
Type	Traditional
Reviewed By Third Party	No
Combination Product	No

Page Last Updated: 06/01/2020

1. Zaawansowana technologia: technologia spiekania złotej cyny,
2. Uchwyty: paski laserowe Niemcy / USA, 10 barów, 1000 w. 12 barów, 1200 W większa

moc dla szybszego i lepszego usuwania włosów, Prawdziwie bezbolesne i trwałe usuwanie włosów, z oczywistymi wynikami. Prawdziwie bezbolesne i trwałe usuwanie włosów, z oczywistymi wynikami.

3. Szybkie leczenie: rozmiar plamki Nig 10*20mm/15*25mm/12*38mm, częstotliwość 1-10Hz, wyższa wydajność

4. Ciągła praca: skraplacz TEC powietrze woda półprzewodnikowy układ chłodzenia, może faktycznie kontrolować stałą temperaturę wody przy 22 ~ 24 °C, upewnij się, że maszyna pracuje nieprzerwanie przez 24 godziny bez zatrzymywania się, nawet latem bez klimatyzatora.

ODM & OEM
Android support



12*36nm
1600W

12*24nm
1200w

1.5*1.5nm



TOP1
HOT PRODUCT





High-quality laser bars imported from Germany

1000/1200/1600ww high power



Fast hair removal




▶ 10bar
1000W



▶ 12bar
1200W



▶ 16bar
1600W



»»Efekt super chłodzenia:

Temperatura szafiru -5 ~ 3 °C. Skutecznie zmniejszają bolesność w zabiegu i sprawiają, że

»»Włochy pompa wodna:

Lepiej dla laserowego kręgu wodnego, zabierz ciepło, dłuższą żywotność.

»»Dwa filtry do wody:

Dwie reakcje wymiany klasy spożywczej, mogą zapewnić jakość wody do obiegu



755nm



808nm



1064nm

